



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	CABLE TIE		DIMENSIONS				COLOR	WEIGHT grams/100pcs
	MIN TENSILE	MAX BUNDLE	'A'	'B' (REF)	'C' (REF)	'D' (REF)		
PUM-049-C2S-_30	50 LBS (222 N)	2.0 " (51 MM)	13.8	7.2	16.5	193	BLACK	140.0



NOTES:

- SEE www.panduit.com FOR CURRENT PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.
- (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
- APPLICATION SPECIFICATION:
A. NOMINAL HOLE DIAMETER: 4.6 - 4.9 mm
B. NOMINAL PANEL THICKNESS: 0.7 - 3.0 mm



SCALE 1:2

TITLE		PUM-049-C2S-_30 PUSH MOUNT/CABLE TIE ASSEMBLY	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		10B015JW/00	
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE METRIC.		PANDUIT	
.X ± 0.5 .XX ± - - -		MATERIAL: HEAT STABILIZED NYLON 6.6	
THIRD ANGLE PROJECTION		DRAWING NUMBER: 10B015JW	
DRAWN BY BWG	DATE 6/04/13	CHK RTFI	SCALE 1:1 UNLESS NOTED
SHT 1 OF 1		SIZE A	

R	6/04/13	BWG	MPH	RTFI	DRAWING RELEASED.	10B015JW/R
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PUM-049-C2S-D30](#)