


TABLE 1			
PART NUMBER	DESCRIPTION	MAX. NO. LOCKS.	STANDARD PKG.
PSL - 1	HASP WITH 1.0" (25 mm) DIA. JAW AND OVERLAPPING TABS	6	12
PSL - 1.5	HASP WITH 1.5" (38 mm) DIA. JAW AND OVERLAPPING TABS	6	12
PSL - 1A	HASP WITH 1.0" (25 mm) DIA. JAW	6	12
PSL - 1.5A	HASP WITH 1.5" (38 mm) DIA. JAW	6	12

TABLE 2				
P/N	"A"	"B" OVERALL	"C"	"D" DIA.
PSL - 1	.375 +/- .063 [9.5 +/- 1.6]	4.50 +/- .12 [114.3 +/- 3.1]	1.00 +/- .04 [25.4 +/- 1.0]	1.50 +/- .04 [38.1 +/- 1.0]
PSL - 1.5		5.05 +/- .12 [128.3 +/- 3.1]	1.50 +/- .04 [38.1 +/- 1.0]	2.12 +/- .04 [53.8 +/- 1.0]
PSL - 1A		4.40 +/- .12 [111.8 +/- 3.1]	1.00 +/- .04 [25.4 +/- 1.0]	1.50 +/- .04 [38.1 +/- 1.0]
PSL - 1.5 A		4.95 +/- .12 [125.7 +/- 3.1]	1.50 +/- .04 [38.1 +/- 1.0]	2.12 +/- .04 [53.8 +/- 1.0]

NOTES:

1. DIMENSIONS SHOWN IN
BRACKETS ARE IN MILLIMETERS.
2. PSL-1A AND PSL1.5A DO NOT HAVE TABS
3. OPERATING TEMPERATURE: -40° C (-40° F) TO 60° C (140° F)



CAD FILENAME/LAYERS										100318MU_DC_C10099/01H		
7	7/7/11	JHAC	<i>John</i>	ADDED OPERATING TEMPERATURE AND MORE DETAIL TO TITLE CHANGED MATERIAL DESCRIPTION, REMOVED ADDITIONAL DIMENSIONAL INFORMATION AND REMOVED VIEW 1 AND VIEW 2	6451	R				 PANDUIT CORP. TINLEY PARK, ILLINOIS		
6	7/21/09	RVU		.375 +/- .062 Ø WAS .375 +/- .125 Ø. C1018 WAS C108. .083/.079 WAS .080/.079. ADD "TABLE 1 & TABLE 2" ONLY. TOL: +/- .04 (+/- 1.01 WAS +/- .12 (+/- 3.1) FOR ALL OF COLUMN "F".	5797	R						
5	7/15/09	RVU		VOID						 SAFETY LOCKOUT HASP - PSL-1(A) AND PSL1.5(A)		
4	10/20/08	RVU	LDG	CHANGE FORMAT 'B' TO 'A'. ADDED NEW COLUMNS OF "G" DIA., "H" R., VIEW 2 AND REVISED NOTES 2.	5571	R						
3	7-27-06	RVU	DWY	ADD TABLE "E" AND "F".	4583	R				UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
2	3-29-05	RVU	DWY	ADDED SIDE VIEW, VIEW 1, AND DIMENSIONS "A", "B", "C" AND "D".	3840	R						
1	3-25-03	RVU	DWY	DIMENSION 1.50 ±.125, 5.00 ±.125, & TOLERANCE ADDED. MISC. REVISIONS.	3207	R				DRAWN BY RVU	MAT'L;  ZINC PLATED STEEL WITH RED PVC COATING	SCALE NTS
R	9-23-99	RVU	DWY	DRAWING RELEASE	1438	R				DATE 9-23-99		DRAWING NO. C10099
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D <i>AK</i>		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PSL-1.5A](#) [PSL-1.5](#)