


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:
1. SEE MFG. DRAWING NO: A61192.

PART NUMBER	MATERIAL	MARKER SIZE inches (mm)	LABELS PER ROW	ROWS PER FANFOLD	STANDARD PKG. QTY.
C100X025YJD	GMY	1.000" [25.40]	7	36	5000
C100X025CBD	GMC	.250" [6.35]			

CAD FILENAME/LAYERS 00472FV_C10229_C100X025xx6_00.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

OPTIMUM C100X025YJD AND C100X025CBD
COMPUTER PRINTABLE LABELS

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) $\pm$.031 (.XXX) $\pm$.005
(.XX) $\pm$.015 ANGLES

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY RVU	MAT'L;
-----------------	--------

MAT'L;

SCALE 1/2

 $1/2$

DATE
9-29-04

AS NOTED

DRAWING NO.

C10229

DWG
A
SIZE

O	9-29-04	RVU		DRAWING RELEASED.	0000	R		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP

CHK'D	
-------	--

C1

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[C100X025YJD](#) [C100X025CBD](#)