



PART NO.	MATERIAL	COLOR	MARKER SIZE	LABELS PER SHEET	SHEET PER PKG.	STANDARD PKG. QTY.
C100X050YJJ	GMY	WHITE	1.00 X 0.500	119	85	10000
C100X050YLJ	GMY	SAFETY YELLOW	1.00 X 0.500	119	43	5000
C100X050YMJ	GMY	SILVER	1.00 X 0.500	119	43	5000
C100X050YQJ	GMY	SILVER	1.00 X 0.500	119	43	5000

1.000 [25.40]  
TYP. 7 PLCS.

1.100 [27.94] REPEAT  
TYP. 6 PLCS.

NOTES:  
1. SEE MFG. DRAWING NO. A61209.  
2. MILLIMETER ARE IN [     ].

CAD FILENAME/LAYERS I00472GM\_C10246\_C100X050YxJ\_00.PRT

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
1	5/2/07	RVU		ADDED "INKJET" ON HEADER.	4971	R		
0	9-30-04	RVU		DRAWING RELEASED.	0000	R		

<b>PANDUIT</b> CORP. TINLEY PARK, ILLINOIS	
<b>OPTIMUM C100X050Y*J LASER/INKJET LABELS</b>	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031    (.XXX) ± .005 (.XX) ± .015    ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
DRAWN BY RVU	MAT'L: SEE TABLE
DATE 9-30-04	SCALE NTS
CHK'D	DWG C10246 SIZE B

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[C100X050YJJ](#) [C100X050YLJ](#)