


CATALOG NUMBER	STRANDED COPPER CONDUCTOR SIZE (AWG)		NO. RIBS	DIMENSIONS - IN [mm]				COLOR CODE	WIRE STRIP LENGTH	INSTALLATION TOOLING		
	RUN	TAP		A	Q	T (MATH THICKNESS)	V			CT-2001	CT-1700**	CT-920, CT-920CH, CT-930, CT-930CH, CT-940CH*, CT-2940*
CTAPF10-16-C	14	16-14	0	.41	.13	.06	.19	RED	1/2	CD-2001-8	RED P21	CT-920, CT-920CH, CT-930, CT-930CH, CT-940CH*, CT-2940*
	12	16-12		[10.4]	[3.3]	[1.5]	[4.8]	[12.7]	RED P21	(2)	-----	
CTAPF8-12-C	10	14	0	.67	.19	.07	.26	BLUE	11/16	CD-2001-6	BLUE P24	-----
	8	12		[17.0]	[4.8]	[1.8]	[6.6]	[17.5]	BLUE P24	(2)	-----	
CTAPF6-12-C	8	10-8	0	.67	.24	.07	.32	GRAY	11/16	CD-2001-4	GRAY P29	-----
	6	12-10		[17.0]	[6.1]	[1.8]	[8.1]	[17.5]	GRAY P29	(2)	-----	
CTAPF4-12-C	6	8-6	1	1.25	.28	.07	.40	BROWN	1-5/16	CD-2001-2	BROWN P33	CDM-920-2
	5,4	12-8		[31.8]	[7.1]	[1.8]	[10.2]	[33.3]	BROWN P33	(4)	BROWN P33M	(1)
CTAPF3-12-C	5,4	6-5	1	1.25	.31	.08	.46	GREEN	1-5/16	CDM-2001-1	GREEN P37	CDM-920-1
	3	12-6		[31.8]	[7.9]	[2.0]	[11.7]	[33.3]	GREEN P37M	(4)	GREEN P37M	(1)
CTAPF2-12-C	4	4	1	1.25	.33	.08	.51	PINK	1-5/16	CDM-2001-1/0	PINK P42	CDM-920-1/0
	3	5		[31.8]	[8.4]	[2.0]	[13.0]	[33.3]	PINK P42M	(4)	PINK P42M	(1)
CTAPF1-12-C	3	4-3	2	1.82	.40	.08	.57	BLACK	1-7/8	CDM-2001-2/0	BLACK P45	CDM-920-2/0
	2	5-4		[46.2]	[10.2]	[2.0]	[14.5]	[47.6]	BLACK P45M	(4)	BLACK P45M	(1)
CTAPF1/0-12-L	2	4-2	2	1.82	.42	.09	.63	ORANGE	1-7/8	CD-2001-3/0	ORANGE P50	CDM-920-3/0
	1	4-3		[46.2]	[10.7]	[2.3]	[16.0]	[47.6]	ORANGE P50M	(4)	ORANGE P50M	(1)
CTAPF2/0-12-Q	1/0	12-4	2	1.82	.48	.09	.71	PURPLE	1-7/8	CD-2001-4/0	PURPLE P54	CDM-920-4/0
	2/0	12-3		[46.2]	[12.2]	[2.3]	[18.0]	[47.6]	PURPLE P54	(4)	PURPLE P54M	(1)
CTAPF3/0-12-Q	1/0	1-1/0	2	1.82	.55	.09	.81	YELLOW	1-7/8	CD-2001-250	YELLOW P62	CDM-920-250
	2/0	2-1		[46.2]	[14.0]	[2.3]	[20.6]	[47.6]	YELLOW P62	(4)	YELLOW P62M	(1)



1. MATERIAL: COPPER
2. UL LISTED AND CSA CERTIFIED FOR APPLICATIONS UP TO 600 VOLTS.
TEMPERATURE RATING 90 °C
3. PACKAGE QTY:
 - C = 100
 - L = 50
 - Q = 25

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CTAPF4-12-C](#) [CTAPF1-12-C](#) [CTAPF10-16-C](#) [CTAPF6-12-C](#) [CTAPF3/0-12-Q](#) [CTAPF2/0-12-Q](#) [CTAPF8-12-C](#)
[CTAPF3-12-C](#) [CTAPF2-12-C](#)