




- NOTES:
- 1. UL LISTED AND CSA CERTIFIED
 - 2. FOR COPPER WIRE ONLY.
 - 3. DIMENSIONS ARE INCHES. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
 - 4. IF HEX KEY IS NOT GIVEN, FLAT HEAD SCREW IS USED.



PANDUIT PART NUMBER	CONDUCTOR RANGE	WIRE DIAMETER RANGE - IN	APPROXIMATE DIMENSIONS - IN [mm]							WRENCH SIZE	TORQUE VALUE
			C	K	H	L	T	W	J		
PNL-4-C	14 SOL - 4 STR	.064-.232	.27 [7]	.27 [7]	.56 [14]	1.25 [32]	.14 [3.57]	.53 [13]	5/16-24	SLOTTED SCREWDRIVER	45
PNL1/0-L	8 SOL - 1/0 STR	.128-.375	.38 [10]	.33 [8]	.78 [20]	1.59 [40]	.14 [3.57]	.73 [16]	1/2-20	1/4"	200
PNL-250-Q	6 SOL - 250 kcmil	.162-.575	.44 [11]	.39 [10]	1.05 [27]	1.97 [50]	.13 [3.17]	.94 [24]	5/8-18	5/16"	275
PNL-500-3	4 SOL - 500 kcmil	.204-.815	.75 [19]	.53 [13]	1.47 [43]	3.00 [76]	.25 [6.35]	1.38 [35]	15/16-16	3/8"	375
PNL-1000-3	500 kcmil - 1000 kcmil	.815-1.153	.69 [17]	.56 [14]	2.00 [51]	3.88 [99]	.38 [9.52]	1.75 [44]	1-3/8-14	1/2"	500

REV	DATE	BY	CHK	DESCRIPTION	ECN
03	9/09	JHNU	JHNU	REMOVED PNL8-C FROM DRAWING CONVERTED DRAWING TO SOLIDWORKS	
02	11/02	CJW		ADDED NEW UL & CSA SYMBOLS, CHANGED MCM TO kcmil CHANGED CATALOG NUMBER TO PANDUIT PART NUMBER	
01	3/01	RM		FILESPEC WAS N41174CA_PCD_00	
00	10/96	TM		DWG. RELEASED	

PANDUIT

CORP. TINLEY PARK, ILLINOIS

CONE SCREW LUG CONNECTOR
CUSTOMER DRAWING

SCALE N/A

DRAWING NO / CAD FILE C41174_03

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PNL-500-3](#) [PNL-1/0-L](#) [PNL-250-Q](#) [PNL-1000-3](#) [PNL-4-C](#)