



PART NUMBER	FOR PANDUIT H-TAPS	DIMENSIONS IN INCHES		
		L	W	H
CLRCVR3-1	HTCT250-8-1 HTCT250-2-1 HTCT250-250-1	5.35	2.16	1.40

LABEL RETAINER
(2) SUPPLIED

FINGERS

COVER
BODY



TWO PIECE CONSTRUCTION
WITH SNAP TOGETHER
LATCHES

NOTES:

- MATERIAL:
CLEAR POLYCARBONATE COVER BODY WITH
BLACK POLYPROPYLENE FINGERS.
A) HIGH IMPACT STRENGTH
B) U.V. RESISTANT
C) FLAMMABILITY RATED (UL94 V-0)
D) LIMITING OXYGEN INDEX
(L.O.I.) = 28 MINIMUM.
- UL LISTED & CSA CERTIFIED:
A) WHEN USED WITH SPECIFIED PANDUIT
H-TAPS
B) MAXIMUM TEMPERATURE RATING OF
INSULATION MATERIAL: 90°C
C) VOLTAGE RATING OF COVER: 600V. MAX.
- COVER PART NUMBER INCLUDES TWO (2) COVER
HALVES, TWO (2) MATTED SURFACE SNAP IN
LABEL RETAINERS, AND TWO (2) CABLE TIES
TO SUPPLEMENT THE MOLDED-IN LATCHES.



LISTED
WIRE CONNECTOR



CERTIFIED

CAD FILENAME/LAYERS
C41474_00

PANDUIT CORP. TINLEY PARK, ILLINOIS

HTAP CLEAR COVER CLRCVR3
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .01 (XXX) ± .01
(.XX) ± .06 ANGLES ± .1

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JHNU

MAT'L:

SCALE
NONE

DATE
12/22/04

SEE NOTES

DRAWING NO.
C41474

DWG
B
SIZE

00	12/04	JHNU		DRAWING RELEASED				
REV	DATE	BY	CHK	DESCRIPTION	ECN	PM	CUST	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CLRCVR3-1](#)