



Mini-Com® Shuttered Surface Mount Boxes

- Accept Mini-Com® Modules for STP and UTP, FJ® Fiber Optic Jack Modules and other flush modules, which snap in and out for easy moves, adds, and changes
- Clear shuttered doors are spring-loaded to stay closed to prevent dust from entering module opening; doors can be collapsed to insert plug into module
- Cable entry from side, rear, and base knockouts
- Mount easily with supplied mounting screws, adhesive tape, or optional magnet (CSBM-X)
- Optional icons available
- Optional adhesive labels available



CBXS1IW-A



CBXS2IW-A



CBXS3IW-AY



CBXS4IW-AY



CBXS6IW-AY



CBXSD6IW-AY

Part Number	Part Description	Color‡	Used with Pan-Way® Raceway	Std. Pkg. Qty.	Std. Ctn. Qty.
CBXS1IW-A	Shuttered surface mount box accepts one Mini-Com® Module. 0.62"H x 1.64"W x 2.47"L (15.75mm x 41.66mm x 62.73mm)	Off White	LD5/LDPH5*	1	10
CBXS2IW-A	Shuttered surface mount box accepts two Mini-Com® Modules. 0.94"H x 2.40"W x 2.5"L (23.88mm x 60.96mm x 63.50mm)	Off White	LD5/LDPH5*	1	10
CBXS3IW-AY	Shuttered surface mount box accepts three Mini-Com® Modules. 0.94"H x 3.62"W x 3.31"L (23.88mm x 92.00mm x 84.00mm)	Off White	LD5/LDPH5	1	10
CBXS4IW-AY	Shuttered surface mount box accepts four Mini-Com® Modules. 0.94"H x 4.65"W x 3.28"L (23.88mm x 118.11mm x 83.31mm)	Off White	LD3/LDPH3 LD5/LDPH5	1	10
CBXS6IW-AY	Shuttered surface mount box accepts six Mini-Com® Modules. 0.94"H x 6.7"W x 3.28"L (23.88mm x 170.18mm x 83.31mm)	Off White	LD3/LDPH3 LD5/LDPH5	1	10
CBXSD6IW-AY	Deep shuttered surface mount box accepts six Mini-Com® Modules (includes cable routing bridge). 1.16"H x 7.58"W x 3.86"L (29.60mm x 192.50mm x 98.00mm).	Off White	LD5/LDPH5 LD10/ LDPH10	1	10

‡For other colors replace suffix IW (Off White) with EI (Electric Ivory), WH (White), IG (International Gray), or BL (Black).

*Raceway does not enter box.

Component Labels for Mini-Com® Shuttered Surface Mount Boxes



Suggested Label Solutions for TIA/EIA-606-A Compliance

Box Part Number	Laser/Ink Jet Desktop Printer Label	TDP43ME Thermal Transfer Desktop Printer Label	PanTher™ LS8E Hand-Held Printer Label	Cougar™ LS9 Hand-Held Printer Label
CBXS1**-A	C061X030FJJ	C061X030YPT	C061X030FJC	T031X000FJC-BK
CBXS2**-A				
CBXS3**-A				
CBXS4**-A				
CBXS6**-A				
CBXSD6**-A				

For complete labeling solutions and product information, reference charts on pages O.1 – O.22 of SA-NCCB51.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CBXS6IW-AY](#) [CBXS4IW-AY](#) [CBXS1IW-A](#) [CBXS3IW-AY](#)