


PANDUIT P/N	WEIGHT
CFPTR2B**	2.59 LB/10 PCS (1174.1 g/10 PCS)

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PARTS INCLUDED:
 - 2- MOUNTING SCREW #6-32 X 1"
(SECURES FACEPLATE TO WALL)
 - 2- TAMPER RESISTANT SCREW
HEX BUTTON HEAD
#6-32 x 1.25"
(SECURES COVER TO BASE)
 - 1- BASE
 - 1- COVER
 - 2- COVER SCREW #6-32 X 1.25"
COMBINATION PAN HEAD
(SECURES COVER TO BASE)



MODEL FILENAME		MO1445AA_CFPTR2B_ASMBLY_02.PRT	SIZE A
DRAWING FILENAME		MO1445AA_DC_02A.PRT	
MINI-COM™ TAMPER RESISTANT FACEPLATE WITH 2 BREAKOUT PORTS CUSTOMER DRAWING			
		I.I. NUMBER	N/A
		PRODUCT SPEC	N/A
	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°	WORK INSTRUCTION	N/A
		SCALE	FULL
DRAWN BY JsP	REVIEW DRAWING NUMBERS	PART NO. CFPTR2B**	
DATE 12-15-04	MATERIAL: PC	DRAWING NO. 01445-02 SHEET 1 OF 2	
CHK'D			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CFPTR2BIW](#) [CFPTR2BWH](#) [CFPTR2BIG](#) [CFPTR2BEI](#)