



Material :

Housing: PBT UL 94V-0, Nature Color
 Inner Plastic: PBT UL 94V-0, Red Color
 Rubber Seal: Silicone Rubber
 Seal Ring: Silicone Rubber

Ordering Code:


CPB2 ** P * R 00
 ① ② ③ ④ ⑤ ⑥











- ① Series No.
- ② No. of Circuits: 02, 03, 04, 06, 08 Pin
- ③ P= Plug Housing
- ④ 0= Single Row (2P, 3P, 4P only)
 D= Dual Row (6P, 8P only)
- ⑤ R= Rubber Seal
- ⑥ Other Option: 00= Standard

Circuits	Dimension
	A
2	—
3	4.00(.157)
4	6.00(.236)
6	4.00(.157)
8	6.00(.236)

RoHS Compliant

④					DATE	UNIT: mm / inch	TITLE:	 瀚荃股份有限公司 CviLux Corporation			
③					DRAWN BY: Clark	7/23-20'	CPB2 Series Plug Housing				
②					ENGINEER: Clark	7/23-20'	MATERIAL:	DRAWING NO.	CPB203SA	PART NO.	CPB2**POR00 CPB2**PDR00
①	Clark	07/15-20	ECNT120185		CHECKED BY: Eisley	7/24-20'	FINISH:	SCALE	4 / 1	SHEET	1 OF 2
SYM	NAME	DATE	REVISIONS		APPROVED BY: Eisley	7/24-20'					





02 PIN

03 PIN

04 PIN

06 PIN

08 PIN

RoHS Compliant

4					DATE	UNIT: mm / inch	TITLE:	 瀚荃股份有限公司 CviLux Corporation			
3				DRAWN BY:	Clark	7/23-20'	CPB2 Series Plug Housing				
2				ENGINEER:	Clark	7/23-20'	MATERIAL:				
1	Clark	07/15-20	ECNT120185	CHECKED BY:	Eisley	7/24-20'	FINISH:				
SYM	NAME	DATE	REVISIONS	APPROVED BY:	Eisley	7/24-20'		SCALE	2 / 1	SHEET	2 OF 2

CVILUX
2020.07.30
ISSUED

TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X ± 0.30/.012	X' ± r'
.XX ± 0.20/.008	.X' ±
.XXX ± 0.10/.004	.XX' ±

DRAWING NO.	CPB203SA	PART NO.	CPB2**POR00 CPB2**PDR00
-------------	----------	----------	----------------------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[CPB24BL](#)