



PANDUIT P/N	WEIGHT
CPP48HDEWBL	6.15 LB/10 PCS (2788.0 g/10 PCS)



NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
2. THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
3. PACKAGE CONTENTS:
 - (1) -48 PORT STAMPING
 - (6) -8 POSITION FACEPLATE (ASSEMBLED TO PANEL)
 - (1) -SCREW KIT (INCLUDES FOUR #12-24 SCREWS AND FOUR LOCK WASHERS)
 - (1) -SCREW KIT (INCLUDES FOUR M6 SCREWS)
4. DIMENSIONS IN PARENTHESIS ARE IN METRIC.



THIS PATCH PANEL WILL ONLY ACCEPT RJ45 COPPER CONNECTORS. FIBER AND AV MODULES WILL NOT FIT CORRECTLY TO ACCEPT THEIR MATING PLUG.



MODEL FILENAME M00741FE_CPP48HDNS_ASSY_00.PRT		SIZE A
DRAWING FILENAME M00741FE_DC_00A.PRT		
MINI-COM 48 PORT HIGH DENSITY MODULAR PATCH PANEL WITH ENHANCED LABELING AREA CUSTOMER DRAWING		
 PANDUIT TM CORP. TINLEY PARK, ILL 60477		I.I. NUMBER N/A
		PRODUCT SPEC N/A
 THIRD ANGLE PROJECTION		WORK INSTRUCTION N/A
ALL DIMENSIONS ARE GIVEN IN INCHES. UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .031(.8) ANGLES ±		SCALE NONE
DRAWN BY JsP	MATERIAL:	PART NO. CPP48HDEWBL
DATE 12-19-05	20 GAGE C.R.S.	DRAWING NO. 00741-118
CHK'D JSP		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CPP48HDEWBL](#)