


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




DETAIL VIEW OF LABEL AREA


PANDUIT P/N	WEIGHT
CPPA48HDEWBL	6.88 LB/10 PCS (3215.2.0 g/10 PCS)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM.
- THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- PACKAGE CONTENTS:
 - (1) - 48 PORT ANGLED STAMPING
 - (6) - 8 POSITION FACEPLATE (ASSEMBLED TO PANEL)
 - (1) - SCREW KIT (INCLUDES FOUR #12-24 SCREWS AND FOUR LOCK WASHERS)
 - (1) - SCREW KIT (INCLUDES FOUR M6 SCREWS)
- DIMENSIONS IN [] ARE IN METRIC.




THIS PATCH PANEL WILL ONLY ACCEPT RJ45 COPPER CONNECTORS. FIBER AND AV MODULES WILL NOT FIT CORRECTLY TO ACCEPT THEIR MATING PLUG.



MODEL FILENAME	M00741FV_CPPA48HDEWBL_00.PRT	SIZE	A
DRAWING FILENAME	M00741FV_DC_00A.PRT		

MINI-COM 48 PORT ANGLED HIGH DENSITY MODULAR PATCH PANEL WITH ENHANCED LABELING AREA
CUSTOMER DRAWING



ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.

DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ± .010(.3)
(.XX) ± .03(.8) ANGLES ±

DRAWN BY
JsP

DATE
8-31-06

CHK'D
MAD

MATERIAL:
STAMPING:
20 GAGE C.R.S.
FACEPLATE: ABS

1.1. NUMBER	N/A
PRODUCT SPEC	N/A
WORK INSTRUCTION	N/A
SCALE	NONE
PART NO.	CPPA48HDEWBL
DRAWING NO.	00741-116

R	8-31-06	JsP	RELEASED TO PRODUCTION	00741-116					
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CPPA48HDEWBL](#)