



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. FOR COPPER TO COPPER CONNECTIONS ONLY.
2. UL LISTED PER UL 486A FOR POWER CONNECTOR APPLICATIONS UP TO 35KV.
3. UL LISTED PER UL 467 FOR GROUNDING AND BONDING AND FOR SUITABLE DIRECT BURIAL IN EARTH OR CONCRETE.
4. UL TEMPERATURE RATING 90 °C
5. UL FLAMMABILITY RATING FOR DVR COVERS IS V-0.
6. CVR COVERS ARE NOTE UL LISTED WITH CTAP CONNECTORS.
7. MATERIAL: HIGH CONDUCTIVITY COPPER
8. PACKAGING QTY CODES: -L= 50
-Q=25
-X=10

9. CT-940CH AND CT-2940 REQUIRE CD-940-DA ADAPTER FOR CD-920 DIES



PANDUIT PART NUMBER	COPPER CONDUCTOR SIZE			DIMENSIONS			TAP COVER P/N (REF)	PANDUIT CRIMP TOOL PART NUMBERS				WIRE STRIP LENGTH (+/-1/32")
MAIN	TAP	W	A	H	DIE PART NO. CT-990H, CT-990CH, CT-990CH*, CT-2940*	DIE PART NO. DIE INDEX NO. (# OF CRIMPS)	DIE PART NO. DIE INDEX NO. (# OF CRIMPS)	CT-2001 PBG	CT-2001-BG PBG	3/4		
CTAP4-8-L	#6-#4 SOL OR STR		0.63	0.46	0.73	CVR6-1	CD900-BG PBG (1)	CD-2001-BG PBG (1)	3/4			
CTAP4-6-L	#6 STR, #4 SOL OR STR		0.63	0.48	0.73	CVR6-1	CD900-BG PBG (1)	CD-2001-BG PBG (1)	3/4			
CTAP4-4-L	#4 SOL OR STR		0.63	0.46	0.81	CVR6-1	CD900-BG PBG (1)	CD-2001-C PC (1)	7/8			
CTAP2-4-Q	#2 SOL OR STR		0.76	0.60	0.96	CVR2-1	CD900-C PC (1)	CD-2001-C PC (2)	7/8			
CTAP2-2-X	#2 SOL OR STR		0.75	0.60	1.05	CVR2-1	CD900-C PC (1)	CD-2001-C PC (2)	7/8			
CTAP2/0-2-X	#1/0-#2/0 STR		0.93	0.80	1.32	CVR2-1	CD900-O PO (1)	***** ***** *****	1-1/16			
CTAP2/0-2/0-X	#1/0-#2/0 STR		0.93	0.80	1.37	CVR250-1	CD900-O PO (1)	***** ***** *****	1-1/16			
CTAP4/0-2-X	#3/0-#4/0 STR		1.08	0.94	1.66	CVR500-1	CD920-03 PD3 (1)	***** ***** *****	1-1/4			
CTAP4/0-2/0-X	#3/0-#4/0 STR		1.08	1.00	1.57	CVR500-1	CD920-03 PD3 (1)	***** ***** *****	1-1/4			
CTAP4/0-4/0-X	#3/0-#4/0 STR		1.08	1.00	1.57	CVR500-1	CD920-03 PD3 (1)	***** ***** *****	1-1/4			

06	4/10	JHNU	JHNU				REVISED DWG NUMBER: 10N002BA-NC WAS C41220 CONVERTED DWG TO SOLIDWORKS REVISED UL LABEL	10N002BA-NC	FLD
05	10/09	JESH	JESH				UPDATED TABLE TAP COVER P/N REF. TAP/C COVERS ARE REPLACED WITH CVR COVERS		
							ADDED NOTES		
04	2/02	SAB					ADDED DB TO THE STAMP, ADDED NOTES 6 & 7	09827	LM JAC
03	1/02	SAB	JAC				ADDED WIRE CONNECTOR UNDER THE UL SYMBOL	09788	LM JAC
02	11/01	BDK	RLS				REMOVED CTAP2-4-L, CTAP2-2-L, ADDED TOOLING INFORMATION AND UPDATED TABLE. UPDATED THE NOTES, AND ADDED BLACK INK MARKINGS LEADER.		
01	5/01	ED	SKB				REVISED TABLE TO REFLECT PRODUCT EXPANSION	09328	JAC
00	9/97	TM	WJB				RELEASED	09354	JAC
REV	DATE	BY	CHK	DESCRIPTION					

PANDUIT CORP. TINLEY PARK, ILLINOIS
CTAP COPPER COMPRESSION TAPS
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (X) ± (XX) ± ANGLES ±		DRAWN BY: TSM/A	DATE: 9/97	CHK'D: WJB	SCALE: NONE	DWG NO: 10N002BA-NC	DWG SIZE: B
---	--	-----------------	------------	------------	-------------	---------------------	-------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CTAP4/0-2-X](#) [CTAP2-4-Q](#) [CTAP4/0-2/0-X](#) [CTAP2/0-2/0-X](#) [CTAP2/0-2-X](#) [CTAP4-6-L](#) [CTAP4-4-L](#) [CTAP4/0-4/0-X](#)
[CTAP2-2-X](#) [CTAP4-8-L](#)