


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	STUD SIZE	DIMENSIONS - in [mm]				
		A ± [0,8]	W ± [0,3]	C ± [0,4]	M ± [0,5]	H ± [0,3]
PV22-4F	#4	.67 [17,02]	.20 [5,08]	.21 [5,33]	.56 [14,22]	.12 [3,05]
PV22-6F	#6	.76 [19,30]	.25 [6,35]	.26 [6,60]	.62 [15,75]	.14 [3,56]

INSTALLATION TOOLS
CT-520
CT-1525 (A POCKET)
CT-2500 (CT-2525CH: A PKT)



NOTES:

1. RECOMMENDED FOR:

- A. #26-22 AWG SOLID OR STRANDED COPPER WIRE
- B. 221° F (105°C) MAX TEMP. RATING
- C. 600V MAX VOLTAGE RATING


2. MATERIAL:

- A. STAMPING - .02" [0,5] THK COPPER, TIN PLATED
- B. HOUSING - VINYL, YELLOW

3. SEE www.panduit.com FOR PACKAGE QUANTITIES

4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS

5. WIRE STRIP LENGTH: $3/16" \begin{smallmatrix} +1/32" \\ -0 \end{smallmatrix} [4,8mm \begin{smallmatrix} +0,8 \\ -0 \end{smallmatrix}]$

TITLE					
FORK TERMINAL, VINYL INSULATED #26-22 AWG CUSTOMER DRAWING					
ITEM REVISION NAME			PANDUIT		
N41232BA/11					
DATASET FILE NAME			N41232BA/11		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			MATERIAL:		
.X ± .XX ± 			.XXX ± ANGLES ± THIRD ANGLE PROJECTION		
DRAWN BY			DRAWING NUMBER:		
DAW			A41232		
DATE		CHK	SCALE	SHT 1 OF 1	SIZE
		CH	N/A		A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
11	8/19	MRJS	SKB	JADE	REMOVED NOTE WITH RoHS DIRECTIVE NUMBER - SEE WEBSITE	051121/00
10	4/15	JHNU	TMR	RGB	ADDED CT-2500 TOOL, UPDATED TOOL FORMAT	N41232BA-DC
09	1/15	JHNU	TMR	RGB	ADDED WIRE STRIP LENGTH NOTE REVISED TITLE BLOCK	N41232BA-DC



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PV22-4F-MYY](#)