




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	WEIGHT (APPROX.)
DP246X88TGY	1.25 lb (567 g)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
- MATERIAL:
PANEL HOUSING: STEEL
RJ45 MODULE: THERMOPLASTIC RESIN UL94V-0
PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
- 24 PORT PATCH PANEL 8 POSITION 8 WIRE.
- THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) METRIC M6x1x15MM SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- USE 110 STYLE TERMINATION TOOL FOR PUNCH DOWN.
- RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.

MODEL FILENAME M02088AA_1RU_24PORT_PANEL_ASSY_04		SIZE A
DRAWING FILENAME M02479JB_DC238/00B		
TITLE DP6A 10GIG 24 PORT PATCH PANEL CUSTOMER DRAWING		
 PANDUIT ™ CORP. TINLEY PARK, IL 60477		I.I. NUMBER
		PRODUCT SPEC
		WORK INSTRUCTION
 THIRD ANGLE PROJECTION		SCALE .25:1
DRAWN BY LZ		PART NO. SEE CHART
DATE 3-4-06		DRAWING NO. 02479-238
CHK'D CEF		

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
1	12-2-08	BJN	EJH	A. DP6A 10GIG WAS DP6 10GIG™	02479-238				
R	3-4-06	LZ	CEF	RELEASED TO PRODUCTION	02479-238	CEF	CEF		CEF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[DP246X88TGY](#)