



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
E4X4**2 (SEE NOTE 1)	78.74 IN ±.18 IN (2000.0mm ±4.6mm)	3.94 LB (1787g)	0.60 LB/FT (8.9g/cm)
E4X4**6 (SEE NOTE 1)	72.00 IN ±.18 IN (1828.8mm ±4.6mm)	3.60 LB (1633g)	0.60 LB/FT (8.9g/cm)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D35245CR_DC_E4X4_00.prt

CAD_FILENAME/LAYERS

E4X4 . pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS

FIBER-DUCT 4x4 SLOTTED WALL
CHANNEL (E4X4**2, E4X4**6)

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

$$\begin{array}{l} (.X) \pm \\ (.XX) \pm .03 \quad (0.8) \end{array} \quad \begin{array}{l} (.XXX) \pm \\ \text{ANGLES} \pm \end{array}$$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY	
----------	--

MAT'L:	
--------	--

SCALE

NONE

MSO

DATE	1-5-07
------	--------

CHK'D	RN
-------	----

PVC

DRAWING NO.

35245 - 44

DWG
A
SIZE

R	1-5-07	MSO	RN	RELEASED TO PRODUCTION	35245-44	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	GMBH	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[E4X4LG6](#) [E4X4OR6](#)