


PANDUIT PART NUMBER	WEIGHT
F2PCLB12	0.57 LB/EACH (259g/EACH)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
- THE FIBER ROUTING 2-PIECE LADDER RACK BRACKET IS USED TO SUPPORT FIBER-DUCT AND FIBERRUNNER MOUNTING BRACKETS DIRECTLY FROM A 3/8"×1 1/2" OR A 3/8"×2" LADDER RACK STRINGER WITH THE USE OF 1/2" THREADED ROD (NOT INCLUDED).
- THE FIBER ROUTING 2-PIECE LADDER RACK BRACKET INCLUDES:
TWO (2) BRACKET CLIPS,
TWO (2) 1/2" HELICAL SPRING LOCKWASHERS,
TWO (2) 1/2-13 HEAVY HEX NUTS.
- FINISH COLOR: BLACK (EXCEPT FOR HARDWARE).
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D38192B1_DC/02 F2PCLB12

CAD FILENAME/LAYERS **F2PCLB12.pdf**

PANDUIT CORP TINLEY PARK, ILLINOIS
 FIBER ROUTING 2-PIECE LADDER RACK BRACKET - 1/2 THREADED ROD (F2PCLB12)
 CUSTOMER DRAWING

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	GMBH
2	1-14-08	MSO	RN	E. REMOVED ALL REFERENCES TO F2PCLB12M.	38192-06	RN	RN		
-	-----	---	--	D. REVISED GENERAL NOTES. C. REVISED DRAWING TITLE.	-----	--	--		
1	12-23-05	MSO	RN	B. REVISED CAD FILENAME. A. REV'D DWG. TO CUR. STAND.	38192-06	RN	RN		
R	11-9-01	JHNU	CVV	RELEASED TO PRODUCTION	38192-06	HIW	HIW		

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± .03 (.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY JHNU	MAT'L: STEEL	SCALE NONE	
DATE 11-9-01	CHK'D CVV	DRAWING NO. 38192-06	DWG A SIZE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[F2PCLB12](#)