


PANDUIT PART NUMBER	WEIGHT
F2PCLB58	0.68 LB/EACH (307g/EACH)

NOTES:



- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
- THE FIBER ROUTING 2-PIECE LADDER RACK BRACKET IS USED TO SUPPORT FIBER-DUCT AND FIBERRUNNER MOUNTING BRACKETS DIRECTLY FROM A 3/8"x1 1/2" OR A 3/8"x2" LADDER RACK STRINGER WITH THE USE OF 5/8" THREADED ROD (NOT INCLUDED).
- THE FIBER ROUTING 2-PIECE LADDER RACK BRACKET INCLUDES:
TWO (2) BRACKET CLIPS,
TWO (2) 5/8" HELICAL SPRING LOCKWASHERS,
TWO (2) 5/8"-11 HEAVY HEX NUTS.
- FINISH COLOR: BLACK (EXCEPT FOR HARDWARE).
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D38192BJ_DC/02 F2PCLB58

CAD FILENAME/LAYERS

F2PCLB58.pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS
FIBER ROUTING 2-PIECE LADDER RACK
BRACKET - 5/8" THREADED ROD
(F2PCLB58)
CUSTOMER DRAWING



UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ± (.XXX) ±
(.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
JHNU

MAT'L:

DATE
11-9-01

CHK'D
CVV

STEEL

SCALE
NONE

DRAWING NO.
38192-07

DWG
A
SIZE

3	1-14-08	MSO	RN	F. REMOVED ALL REFERENCES TO F2PCLB58M.	38192-07	RN	RN		
-	-----	---	--	E. REVISED GENERAL NOTES. D. REVISED DRAWING TITLE.	-----	--	--		
2	12-23-05	MSO	RN	C. REVISED CAD FILENAME. B. REV'D DWG. TO CUR. STAND.	38192-07	RN	RN		
1	1-25-02	JHNU	CVV	A. REVISED GENERAL NOTE 1.	38192-07	RN	RN		
R	11-9-01	JHNU	CVV	RELEASED TO PRODUCTION	38192-07	HIW	HIW		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMBH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

F2PCLB58