


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

900um BUFFERED FIBER OPTIC SC/APC PIGTAIL							
PANDUIT PART NO.	BUFFERED FIBER				SC/APC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	RL	COLOR
F9B3A-NM*	NO FLAME RATING	9/125um OSI	SIMPLEX 900um BUFFERED FIBER	BLUE	0.50dB	65dB	GREEN

* - DENOTES PIGTAIL LENGTH, WHERE M = METERS AND F = FEET

										900um BUFFERED FIBER OPTIC SC/APC PIGTAIL CUSTOMER DRAWING		
											 TINLEY PARK, ILL 60477	
										 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (0.3) (.XX) ±.03 (0.8) ANGLES	
										DRAWN BY MC	REVIEW DRAWING NUMBERS	
R	06-14-07	MC		RELEASED TO PRODUCTION	02779-40					DATE 06-08-07	PART NO. SEE TABLE	
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	OTH	CHK'D	DRAWING NO. 02779-40 (SHT. 2 of 2)	SIZE A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[F9B3A-NM3](#) [F9B3A-NM5](#) [F9B3A-NM2](#)