


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

SIMPLEX FIBER OPTIC SC/APC PIGTAIL							
PANDUIT PART NO.	CABLE				SC/APC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	RL	COLOR
F9F3A-NM*	RISER (OFNR)	9/125um OS1	SIMPLEX 1.6mm	YELLOW	0.50dB	65dB	GREEN
F9S3A-NM*	RISER (OFNR)	9/125um OS1	SIMPLEX 3.0mm	YELLOW	0.50dB	65dB	GREEN

* - DENOTES PIGTAIL LENGTH, WHERE M = METERS AND F = FEET

										SIMPLEX FIBER OPTIC SC/APC PIGTAIL CUSTOMER DRAWING		
												
											ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.	
											DRAWING FILENAME M02779CL_DC_00A.prt	
										THIRD ANGLE PROJECTION	SCALE NONE	
										DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (0.3) (.XX) ± .03 (0.8) ANGLES	REVIEW DRAWING NUMBERS	
										DRAWN BY MC	PART NO. SEE TABLE	
R	06-14-07	MC		RELEASED TO PRODUCTION	02779-41					DATE 06-08-07	DRAWING NO. 02779-41 (SHT. 2 of 2)	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D	SIZE A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[F9S3A-NM1](#) [F9S3A-NM3](#) [F9S3A-NM5](#) [F9F3A-NM2](#) [F9S3A-NM2](#) [F9F3A-NM3](#)