






PANDUIT PART NUMBER	TYPE	FOR USE WITH
FLCDSBUY	SINGLEMODE	9/125um FIBER
FLCDBLY	MULTIMODE	50/125um FIBER
FLCDMEIY	MULTIMODE	62.5/125um FIBER

## NOTES:

1. SEE CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. ACCEPTS 1.6/2.0mm, 9/125um SINGLEMODE, 50/125um MULTIMODE OR 62.5/125um MULTIMODE GLASS OPTICAL FIBER.
3. FULLY COMPLIES WITH THE FIBER OPTIC CONNECTOR PERFORMANCE REQUIREMENTS AS SPECIFIED BY TIA/EIA-568-B.3.
4. MATERIAL:  
BODY/HARDWARE: PLASTIC  
BOOT: THERMOPLASTIC RUBBER  
FERRULE: ZIRCONIA CERAMIC
5. DIMENSIONS IN BRACKETS ARE METRIC [mm].
6. WEIGHT PER 10 PIECES, .069 lb [16.7g]



											FIBER OPTIC SINGLEMODE/MULTIMODE DUPLEX LC CONNECTOR CUSTOMER DRAWING			
												 <b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477		
												 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (0.3) (.XX) ± .03 (0.8) ANGLES	
													DRAWING FILENAME M01371AA_DC-Y/08A	
													SCALE NONE	
											DRAWN BY MC	REVIEW DRAWING NUMBERS		
											DATE 03-07-07	PART NO. FLCDSBUY FLCDBLY/FLCDMEIY		
												DRAWING NO. 01371-48	SIZE A	
2	09-01-11	MC	MTV	RELEASED TO PRODUCTION	01371-48	MTV	RWB							
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D JDK				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[FLCDMBLY](#) [FLCDSBUY](#)