

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

HINGED SLOTTED CHANNEL

72.00
[1828.8]

ADJUSTABLE "Z" BRACKET

END CAP

HINGED COVER

WIRE RETAINER

PANDUIT PART NUMBER	WEIGHT
FRHD2KT	3.82 LB/EACH (1734g/EACH)


NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER HINGED DUCT 2x2 KIT CONTAINS THE FOLLOWING:
ONE (1) FIBERRUNNER 2x2 HINGED SLOTTED CHANNEL (H2X2**6),
ONE (1) FIBERRUNNER 2x2 HINGED COVER (HC2**6),
SIX (6) PANDUCT TYPE H WIRING DUCT 2" (50.8) WIRE RETAINERS (WR2H-C),
ONE (1) PANDUCT TYPES H AND HS 2x2 WIRING DUCT END CAP (FHDEC2X2),
FOUR (4) FIBER ROUTING ADJUSTABLE "Z" BRACKETS (FZBA1.5X4).
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.

ENG. REF.: D39279BA_DC_FRHD2KT_01.prt

CAD FILENAME/LAYERS

FRHD2KT.pdf

 $\frac{A}{B}$

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER HINGED DUCT 2x2 KIT CONTAINS THE FOLLOWING:
 - ONE (1) FIBERRUNNER 2x2 HINGED SLOTTED CHANNEL (H2X2**6),
 - ONE (1) FIBERRUNNER 2x2 HINGED COVER (HC2**6),
 - SIX (6) PANDUCT TYPE H WIRING DUCT 2" (50.8) WIRE RETAINERS (WR2H-C),
 - ONE (1) PANDUCT TYPES H AND HS 2x2 WIRING DUCT END CAP (FHDEC2X2),
 - FOUR (4) FIBER ROUTING ADJUSTABLE "Z" BRACKETS (FZBA1.5X4).
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.

CAD FILENAME/LAYERS		FRHD2KT.pdf	
PANDUIT CORP TINLEY PARK, ILLINOIS			
FIBERRUNNER HINGED DUCT 2x2 KIT (FRHD2KT) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± .03 (.8) ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY	MAT'L:	SCALE	NONE
DATE		DRAWING NO.	
10-19-05		39279-01	A
CHK'D			
DJWA			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FRHD2KTYL](#) [FRHD2KTBL](#) [FRHD2KTOR](#)