




PANDUIT
PART NUMBER

WEIGHT

FROVRA12X4

1.00 LB/EACH
(453g/EACH)
NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 12x4 OUTSIDE VERTICAL RIGHT ANGLE FITTING IS DESIGNED WITH A MINIMUM 2" (50.8) BEND RADIUS TO PROTECT FIBER OPTIC CABLES.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D37617CO_DC_FROVRA12X4_01.prt

CAD FILENAME/LAYERS



FROVRA12X4.pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS

**FIBERRUNNER 12x4 OUTSIDE VERTICAL
RIGHT ANGLE FITTING (FROVRA12X4)**

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ± .03 (.8) ANGLES ±
UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.DRAWN BY
JHNU

MAT'L:

DATE
1-4-01

ABS

SCALE
NONEDRAWING NO.
37617-80DWG
A
SIZE

D. REVISED GENERAL NOTES
C. REVISED PART WEIGHT

B. REVISED CAD FILENAME
A. REVISED AND REDRAWN

37617-80

RN

RN

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	GMBH
-	-----	---	---	D. REVISED GENERAL NOTES C. REVISED PART WEIGHT	-----	--	--		
1	7-10-06	DTP	RN	B. REVISED CAD FILENAME A. REVISED AND REDRAWN	37617-80	RN	RN		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FROVRA12X4BL](#) [FROVRA12X4OR](#)