






PANDUIT PART NUMBER	WEIGHT
FRSSM2	0.07 LB/EACH (34g/EACH)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER SLACK SPOOL MANAGER - 2.37" (60.3) DIAMETER IS DESIGNED WITH A MINIMUM 2" (50.8) BEND RADIUS TO PROTECT FIBER OPTIC CABLES.
3. THE FIBERRUNNER SLACK SPOOL MANAGER - 2.37" (60.3) DIAMETER INCLUDES:
ONE (1) SLACK SPOOL,
ONE (1) 1/4-20x1/2 HEX HEAD CAP SCREW,
ONE (1) 1/4 SAE FLAT WASHER,
ONE (1) 1/4-20 HEX KEPS NUT
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D38419BE_DC_FRSSM2_01.prt

CAD_FILENAME/LAYERS

△ FRSSM2 . pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS
FIBERRUNNER SLACK SPOOL MANAGER
- 2.37" (60.3) DIAMETER (FRSSM2)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) ±	(.XXX) ±
(.XX) ±.03	(.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY	MSO
DATE	12-17-02
CHK'D	RPA

MAT'L:

PVC

SCALE	NONE
-------	------

DRAWING NO.
38419-02

DWG
A
SIZE

-	-----	---	---	D. DIMENSIONED MOUNTING HOLE C. REVISED GENERAL NOTES	-----	--	--			
1	7-21-06	DTP	RN	B. REVISED PART WEIGHT A. REVISED CAD FILENAME	38419-02	RN	RN			
R	12-17-02	MSO	RPA	RELEASED TO PRODUCTION	38419-02	RN	RN			
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	GMB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[FRSSM2](#)