





NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 12x4 "Y" TRANSITION WITH 6" EXITS IS DESIGNED WITH A MINIMUM 2" (50.8) BEND RADIUS TO PROTECT FIBER OPTIC CABLES.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.

PANDUIT PART NUMBER	WEIGHT
FRY126	1.43 LB/EACH (647g/EACH)



ENG. REF.: D37617DP_DC_FRY126_01.prt

CAD FILENAME/LAYERS

FRY126.pdf

PANDUIT CORP. TINLEY PARK, ILLINOIS
FIBERRUNNER 12x4 "Y" TRANSITION
WITH 6" EXITS (FRY126)
 CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
 DIMENSIONAL TOLERANCES ARE:

(.X) ± (.XXX) ±
 (.XX) ± .03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,
 ALL DIMENSIONS ARE GIVEN IN
 INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
 JHNU

MAT'L:

DATE
 2-13-01

ABS

SCALE
 NONE

DRAWING NO.
 37617-100

DWG
 A
 SIZE

-	-----	---	---	G. ADDED DIMENSIONS	-----	--	--		
-	-----	---	---	F. REMOVED DIMENSIONS E. RELOCATED DIMENSIONS	-----	--	--		
-	-----	---	---	D. REVISED PART WEIGHT C. REVISED GENERAL NOTES	-----	--	--		
1	7-20-06	DTP	RN	B. REVISED CAD FILENAME A. REVISED DRAWING TITLE	37617-100	RN	RN		
R	2-13-01	JHNU	CEO	RELEASED TO PRODUCTION	37617-100	HIW	HIW		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMBH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FRY126YL](#) [FRY126BL](#)