




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	CABLE TIE			PUSH MOUNT MATERIAL	DIMENSIONS				COLOR	WEIGHT grams/100pcs
	MIN TENSILE	MAX BUNDLE	MATERIAL		'A'	'B'	'C' (REF)	'D' (REF)		
PUM071-RIS-_30	50 LBS (222 N)	1.0 " (51 MM)	NYLON 6.6 WEATHER RESISTANT BLACK	NYLON 6.6 HEAT STABILIZED BLACK	16.9	10.4	16.5	122	BLACK	133
PUM071-R15S-_30	50 LBS (222 N)	1.5 " (51 MM)	NYLON 6.6 HEAT STABILIZED BLACK		16.9	10.4	16.5	160	BLACK	156



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
- APPLICATION SPECIFICATION:
A. NOMINAL HOLE DIAMETER: 6.3 - 7.1 mm
B. NOMINAL PANEL THICKNESS: 0.8 - 7.0 mm

CAD FILENAME/LAYERS		G03597AA_DC_GB3597AA/00C	
PANDUIT CORP. TINLEY PARK, ILLINOIS			
PUM071-RIS-_30 & PUM071-R15S-_30 PUSH MOUNT/CABLE TIE ASSEMBLY			
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN METRIC TOLERANCE: ±0.5MM			
DRAWN BY PSG		SCALE 1:1	
DATE 10/1/08			
CHK'D KLN		SEE TABLE	
		DRAWING NO. GB3597AA	
		DWG A SIZE	

OOC	11/7/08	PSG	RR	CHANGED DIMENSION 'D'	GB3597AA	OOC	KLN		
OOB	10/29/08	PSG		CHANGED PANDUIT PART NUMBERS AND MATERIALS	GB3597AA	OOB			
OOA	10/6/08	PSG		INITIAL RELEASE	GB3597AA	OOA			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PUM071-R1S-C30](#) [PUM071-R1S-D30](#) [PUM071-R15S-D30](#) [PUM071-R15S-C30](#)