


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE PACKAGE QUANTITY.
2. PATCH CORDS CAN BE USED WITH GIGA-PUNCH FOUR-PAIR CONNECTING BLOCKS.
3. THE GIGA-PUNCH PATCH CORD IS POLARIZED TO PREVENT REVERSE INSTALLATION TO THE CONNECTOR BLOCK, INCORPORATES A CABLE JACKET RETENTION FEATURE WHICH MINIMIZES WIRE UNTWISTING, AND HAS AN INTEGRAL STRAIN RELIEF.
4. PATCH CORDS CONSTRUCTED USING UL OR ETL VERIFIED CABLE.
5. MATERIAL:

CONNECTOR: POLYCARBONATE
CABLE: CAT6, 24 AWG STRANDED-TIN/COPPER
JACKET: PVC
JACKET COLOR: WHITE



PANDUIT P/N	LENGTH (MIN) FEET (mm)	WEIGHT LB/10 PCS (530 g/10 PCS)
GPPC41G3Y	3 FT. (914mm)	1.17 LB/10 PCS (530 g/10 PCS)
GPPC41G5Y	5 FT. (1524mm)	1.70 LB/10 PCS (772 g/10 PCS)
GPPC41G7Y	7 FT. (2134mm)	2.17 LB/10 PCS (984 g/10 PCS)
GPPC41G9Y	9 FT. (2743mm)	2.70 LB/10 PCS (1228 g/10 PCS)
GPPC41G14Y	14 FT. (4267mm)	4.03 LB/10 PCS (1827 g/10 PCS)
GPPC41G20Y	20 FT. (6096mm)	5.82 LB/10 PCS (2550 g/10 PCS)
GPPC41G1MY	1 METER	.97 LB/10 PCS (439 g/10 PCS)
GPPC41G2MY	2 METERS	1.77 LB/10 PCS (795 g/10 PCS)
GPPC41G3MY	3 METERS	2.45 LB/10 PCS (1111 g/10 PCS)
GPPC41G5MY	5 METERS	3.93 LB/10 PCS (1783 g/10 PCS)

CAD FILENAME/LAYERS M02479NT_DC358_00A.PRT

PANDUIT
CORP. TINLEY PARK, ILLINOIS
GIGA-PUNCH(TM) PATCH CORDS
(GPPC41G**Y) CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.XX) ± .031(.81) ANGLES ±
(.XX) ± .031(.81) ANGLES ±
UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	3-21-06	NER		RELEASED FOR PRODUCTION	02479-358				
				SEE NOTES					
				SCALE NONE					
				DRAWING NO. 02479-358					
				SIZE A					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[GPPC4IG3Y](#) [GPPC4IG5Y](#) [GPPC4IG9Y](#) [GPPC4IG7Y](#) [GPPC4IG20Y](#) [GPPC4IG14Y](#)