


PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
HC2**2 (SEE NOTE 1)	78.74 IN \pm .18 IN (2000.0mm \pm 4.6mm)	0.79 LB (358g)	0.12 LB/FT (1.8g/cm)
HC2**6 (SEE NOTE 1)	72.00 IN \pm .18 IN (1828.8mm \pm 4.6mm)	0.72 LB (327g)	0.12 LB/FT (1.8g/cm)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D38258CH_DC_HC2_00.prt

CAD FILENAME/LAYERS		HC2.pdf	
PANDUIT		CORP	
FIBERRUNNER 2x2 HINGED COVER		TINLEY PARK, ILLINOIS	
(HC2**2, HC2**6)		CUSTOMER DRAWING	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) \pm (.XXX) \pm (.XX) \pm .03 (0.8) ANGLES \pm		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY MSO		SCALE NONE	
DATE 1-8-07		DRAWING NO. 38258-23	
CHK'D RN		DWG A	

R	1-8-07	MSO	RN	RELEASED TO PRODUCTION	38258-23	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMBH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[HC2OR6](#)