







PANDUIT PART NO.	BUNDLE DIA. MIN-MAX.	DIMENSIONS				WEIGHT grams 100 pcs
		'A'	'B'	'C'	'D'	
HCAG04B06-___20	4 - 6	8.0	12.4	5.1	13.0	164




SCALE: FULL




NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, AND COLOR.
- MATERIAL:
CLIP - NYLON 6/6
GASKET - TPE (STYRENIC BASED ELASTOMER)
COLOR: BLACK
- HOLE DIAMETER: 6.5 - 6.7
PANEL THICKNESS: 0.5 - 0.7
- (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINKMARKS.



VIEW A-A



VIEW A-A

CAD FILENAME/LAYERS		G01932BH_PB_HCAG04B06_05	
		TINLEY PARK, ILLINOIS	
HARNESS CLIP WITH PUSH MOUNT ANCHOR AND GASKET			
Unless otherwise specified, all dimensions are metric tolerance; ±0.5mm			

5	2-28-06	TMSA		REMOVED INSERTION FORCE DIMENSION	GB1932BH	5				DRAWN BY	JAD	MAT'L:	SEE NOTE 2	SCALE	2X
4	4/28/03	JAD		COMPLETELY REVISED, REMOVED GERMAN TEXT	GB1932BH	4				DATE	12-18-98			DRAWING NO.	
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D				GB1932BH	DWG SIZE A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[HCAG04B06-C20](#) [HCAG04B06-D20](#) [HCAG04B06-VM20](#)