




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

|                                                |                                                                                                                                                |
|------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| Material                                       | High Conductivity Seamless Copper Tube                                                                                                         |
| Plating                                        | Electro-Tin                                                                                                                                    |
| Wire Size                                      | 4 AWG, 3 AWG & 2 SOL                                                                                                                           |
| Wire Type                                      | Stranded Copper; Class B: Compact, Compressed or Concentric, Class C: Concentric                                                               |
| Wire Strip Length                              | 1-1/8 in.                                                                                                                                      |
| Stud Size                                      | 3/8 in.                                                                                                                                        |
| UL Listed Wire Connector                       | Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts. |
| UL Temperature Rating                          | 90° C                                                                                                                                          |
| C.S.A Certified Wire Connector                 | Yes                                                                                                                                            |
| Panduit Color Code on Barrel                   | GRAY                                                                                                                                           |
| Panduit Die Index No. on Barrel                | P29                                                                                                                                            |
| Alternate Industry Die Index No. ( ) on Barrel | (8)                                                                                                                                            |



| 01  | 2/03 | SAC | PWS | EXTENDED WIRE RANGE AND UPDATED STAMPS AND MARKINGS | 10543 |
|-----|------|-----|-----|-----------------------------------------------------|-------|
| REV | DATE | BY  | CHK | DESCRIPTION                                         | ECN   |

**PANDUIT CORP. TINLEY PARK, ILLINOIS**

LCC4-38DWF-L  
Copper Lug - Two-Hole, Long Barrel with Window, 90° Angle Tongue

SCALE N/A

DRAWING NO / CAD FILE

LCC4-38DWF-CUST

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[LCC4-38DWF-L](#)