




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL COMPONENTS INCLUDING TOOLKITS AND 1.6/2.0mm AND 3mm BOOT UPGRADES.
2. CONNECTORS ACCEPT 50/125 OR 62.5/125 900 $\mu$ m BUFFERED GLASS OPTICAL FIBER.
3. MATERIAL:  
OUTER HOUSING: PLASTIC  
BOOTS: THERMOPLASTIC RUBBER  
FERRULE: POLYMER  
HARDWARE: BRASS
4. FULLY COMPLIES WITH THE FIBER OPTIC CONNECTOR PERFORMANCE REQUIREMENTS AS SPECIFIED BY TIA/EIA-568-B.3.
5. COMPATIBLE WITH TIA-EIA-604-3 (FOCIS-3)
6. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
7. DIMENSIONS IN BRACKETS ARE METRIC [mm]



PANDUIT PART NUMBER	APPLICATION	PACKAGE QUANTITY
NKFSCMPC6E1	62.5/125 OM1	1 PER BAG 10 PER BOX
NKFSCMPC5BL	50/125 OM2	
NKFSCMPC6E1-C	62.5/125 OM1	100 PER BAG
NKFSCMPC5BL-C	50/125 OM2	



											NETKEY OPTICAM SC CONNECTOR CUSTOMER DRAWING				
												 <sup>TM</sup> CORP. TINLEY PARK, ILL 60477			
												ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.		DRAWING FILENAME M01302AE_DC/00A	
												 THIRD ANGLE PROJECTION	DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (0.3) (.XX) ±.03 (0.8) ANGLES		SCALE NONE
													DRAWN BY EFK	MATERIAL	PART NO. NKFSCMPC♦♦♦ NKFSCMPC♦♦♦-C
R	12-21-09	EFK		RELEASED TO PRODUCTION	01302-68						DATE 12-21-09	DRAWING NO. 01302-68		SIZE A	
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH	CHK'D				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[NKFSCMPC6EI-C](#) [NKFSCMPC5BL](#) [NKFSCMPC6EI](#) [NKFSCMPC5BL-C](#)