

Vinyl Cloth Letters and Numbers



Material Chart

Material	Print Method	Temperature Range	Features
Vinyl Cloth, (PCL,PCLCP)	Pre-Printed	-50°F to 170°F (-46°C to 77°C)	Indoor/outdoor rated; thin conformable material with repositionable adhesive allows label to be removed and reused or used in temporary applications; provides durability, high temperature resistance, and dimensional stability for rough or textured surfaces.

Part Number	Legend	Legend Height		Height		Width		Color (Legend/Background)	Markers Per Card	Std. Pkg. Card(s)	Std. Ctn. Card(s)
		In.	mm	In.	mm	In.	mm				
PCL037-0	0	0.38	9.7	0.50	12.7	0.34	8.7	Black/Yellow	78	25	100
PCL037-1 thru PCL037-9	1 thru 9									25	100
PCL037-0-9	0 thru 9									25	100
PCL037-A thru PCL037-Z	A thru Z									25	100
PCL037-A-Z	A thru Z									25	100
PCLCP037-A-Z	A thru Z									1	4
PCLCP037-0-9	0 thru 9									1	4
PCL037-DSH	—									25	100
PCL062-0	0	0.63	16.0	0.75	19.1	0.56	14.2	Black/Yellow	32	25	100
PCL062-1 thru PCL062-9	1 thru 9									25	100
PCL062-0-9	0 thru 9									1	4
PCL062-A thru PCL062-Z	A thru Z									25	100
PCL062-A-Z	A thru Z									25	100
PCLCP062-0-9	1 thru 5 6 thru 0									1	4
PCLCP062-A-Z	A thru Z									1	4
PCL062-DSH	—									25	100
PCL100-0	0	1.00	25.4	1.50	38.1	0.88	22.4	Black/Yellow	10	25	100
PCL100-1 thru PCL100-9	1 thru 9									25	100
PCL100-0-9	0 thru 9									25	100
PCL100-A thru PCL100-Z	A thru Z									25	100
PCL100-A-J	A thru J									25	100
PCL100-K-T	K thru T									25	100
PCL100-U-Z	U thru Z									25	100
PCLCP100-0-9	1 thru 5 6 thru 0									1	4
PCLCP100-A-Z	A thru Z									1	4
PCL100-DSH	—									25	100
PCL200-0	0	2.00	50.8	2.25	57.2	0.88	22.4	Black/Yellow	10	25	100
PCL200-1 thru PCL200-9	1 thru 9									25	100
PCL200-0-9	0 thru 9									25	100
PCL200-A thru PCL200-Z	A thru Z									25	100
PCL200-A-J	A thru J									25	100
PCL200-K-T	K thru T									25	100
PCL200-U-Z	UK thru TZ									25	100
PCLCP200-0-9	1 thru 5 6 thru 0									1	4
PCLCP200-A-Z	A thru Z									1	4
PCL200-DSH	—									25	100

Table continues on page E5.38

Order number of pieces required, in multiples of Standard Package Quantity.

Prime items appear in **BOLD**.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PCL100-A-J](#) [PCLCP062-0-9](#) [PCL200-9](#) [PRL250YB-A](#) [PCL062-A](#) [PCL200-A](#) [PCL200-Z](#) [PRL250YB-Z](#) [PCL100-0](#)
[PCLCP300-0-9](#) [PCL200-1](#) [PRL150YB-A](#) [PCL100-U-Z](#) [PRL150YB-Z](#) [PCL100-K-T](#) [PCL062-A-Z](#) [PCLCP100-A-Z](#)
[PCL100-DSH](#) [PCLCP200-0-9](#) [PRL250YB-DSH](#) [PCL300-A](#) [PRL150YB-DSH](#) [PCL200-0](#) [PCL062-1](#) [PCL300-0](#)
[PCL300-DSH](#) [PRL250YB-9](#) [PCL062-DSH](#) [PRL150YB-9](#) [PCL300-9](#) [PCL100-Z](#) [PCL200-0-9](#) [PRL150YB-0](#) [PCL200-](#)
[DSH](#) [PCLCP300-A-Z](#) [PCL062-0](#) [PCL062-0-9](#) [PCL200-A-J](#) [PCL200-U-Z](#) [PCL200-K-T](#) [PRL250YB-0](#) [PCLCP062-A-Z](#)
[PCL100-9](#) [PCLCP100-0-9](#) [PCLCP200-A-Z](#) [PCL300-Z](#) [PCL062-9](#) [PCL062-Z](#) [PCL100-A](#) [PCL100-1](#) [PCL100-C](#)