

A. System Overview

Conductor Identification Labels

B1. Cable Ties

Material Chart

| Material | Print Method | Temperature Range | Features |
|-----------|--------------|------------------------------------|--|
| Polyester | Pre-Printed | -40°F to 250°F (-40°C to 121°C) | Indoor/outdoor rated; laminated label material protects legend from abrasion and chemicals; resistant to UV light, chemical atmosphere, and abrasion; excellent life and adhesion properties |

B2. Cable Accessories

B3. Stainless Steel Ties

C1. Wiring Duct

C2. Surface Raceway

C3. Abrasion Protection

C4. Cable Management

D1. Terminals

D2. Power Connectors

D3. Grounding Connectors

E1. Labeling Systems











E2. Labels

E3. Pre-Printed & Write-On Markers

E4. Permanent Identification

E5. Lockout/Tagout & Safety Solutions

F. Index

| Part Number | Symbol | Legend | Marker Diameter | | Labels Per Sheet | Std. Pkg. Sheet(s) | Std. Ctn. Sheet(s) |
|-------------|---|---------------------------|-----------------|-------|------------------|--------------------|--------------------|
| | | | In. | mm | | | |
| PESS-A-CE |  | CE SYMBOL | 0.49 | 12.50 | 20 | 10 | 100 |
| PESS-B-CE | | | 0.63 | 16.00 | 20 | 10 | 100 |
| PESS-C-CE | | | 0.79 | 20.00 | 10 | 10 | 100 |
| PESS-D-CE | | | 0.98 | 25.00 | 10 | 10 | 100 |
| PESS-E-CE | | | 1.24 | 31.50 | 10 | 10 | 100 |
| PESS-A-ES |  | EARTH (GROUND) | 0.49 | 12.50 | 20 | 10 | 100 |
| PESS-B-ES | | | 0.63 | 16.00 | 20 | 10 | 100 |
| PESS-C-ES | | | 0.79 | 20.00 | 10 | 10 | 100 |
| PESS-D-ES | | | 0.98 | 25.00 | 10 | 10 | 100 |
| PESS-E-ES | | | 1.24 | 31.50 | 10 | 10 | 100 |
| PESS-A-L1 |  | OUTER CONDUCTOR – L1 | 0.49 | 12.50 | 20 | 10 | 100 |
| PESS-B-L1 | | | 0.63 | 16.00 | 20 | 10 | 100 |
| PESS-C-L1 | | | 0.79 | 20.00 | 10 | 10 | 100 |
| PESS-D-L1 | | | 0.98 | 25.00 | 10 | 10 | 100 |
| PESS-E-L1 | | | 1.24 | 31.50 | 10 | 10 | 100 |
| PESS-A-L2 |  | OUTER CONDUCTOR 2 – L2 | 0.49 | 12.50 | 20 | 10 | 100 |
| PESS-B-L2 | | | 0.63 | 16.00 | 20 | 10 | 100 |
| PESS-C-L2 | | | 0.79 | 20.00 | 10 | 10 | 100 |
| PESS-D-L2 | | | 0.98 | 25.00 | 10 | 10 | 100 |
| PESS-E-L2 | | | 1.24 | 31.50 | 10 | 10 | 100 |
| PESS-A-L3 |  | OUTER CONDUCTOR 3 – L3 | 0.49 | 12.50 | 20 | 10 | 100 |
| PESS-B-L3 | | | 0.63 | 16.00 | 20 | 10 | 100 |
| PESS-C-L3 | | | 0.79 | 20.00 | 10 | 10 | 100 |
| PESS-D-L3 | | | 0.98 | 25.00 | 10 | 10 | 100 |
| PESS-E-L3 | | | 1.24 | 31.50 | 10 | 10 | 100 |
| PESS-A-LF |  | LEAD FREE SYMBOL | 0.49 | 12.50 | 20 | 10 | 100 |
| PESS-A-N |  | NEUTRAL CONDUCTOR – N | 0.49 | 12.50 | 20 | 10 | 100 |
| PESS-B-N | | | 0.63 | 16.00 | 20 | 10 | 100 |
| PESS-C-N | | | 0.79 | 20.00 | 10 | 10 | 100 |
| PESS-D-N | | | 0.98 | 25.00 | 10 | 10 | 100 |
| PESS-A-PE |  | PROTECTIVE CONDUCTOR – PE | 0.49 | 12.50 | 20 | 10 | 100 |
| PESS-A-ROHS |  | RoHS WHEELED BIN SYMBOL | 0.49 | 12.50 | 20 | 10 | 100 |
| PESS-A-SS |  | SAFETY FUNCTION | 0.49 | 12.50 | 20 | 10 | 100 |
| PESS-B-SS | | | 0.63 | 16.00 | 20 | 10 | 100 |
| PESS-C-SS | | | 0.79 | 20.00 | 10 | 10 | 100 |
| PESS-D-SS | | | 0.98 | 25.00 | 10 | 10 | 100 |

Order number of cards required.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PESS-A-ES](#) [PESS-A-ROHS](#) [PESS-A-SS](#) [PESS-C-ES](#)