





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
PZAEWM3	63.2 LB/EACH PC (28.7 Kg/EACH PC)



NOTES:

1. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.
3. PART INCLUDES:
 - 1- ENCLOSURE BASE
 - 1- ENCLOSURE DOOR
 - 36"- EDGE GROMMET
 - 10- TAK-TY'S™
 - 4- BEND RADIUS CLIP
 - 1- GROUNDING STRAP
 - 1- GROUNDING HARDWARE
 - 2- PORT ID LABEL
 - 1- DOOR LATCH AND HARDWARE
 - 2- SET OF HINGES AND HARDWARE
 - 1- WALL TEMPLATE



MODEL FILENAME	MO1247AO_PZAEWM3_03.PRT	SIZE
DRAWING FILENAME	MO1247AO_DC_03A.PRT	A

PANZONE™ ACTIVE WALL MOUNT
ENCLOSURE CUSTOMER DRAWING

 <div>PANDUIT™ CORP. TINLEY PARK, ILL 60477</div>		I.I. NUMBER N/A	
		PRODUCT SPEC N/A	
		WORK INSTRUCTION N/A	
		SCALE NONE	
 <div>THIRD ANGLE PROJECTION</div>		PART NO. PZAEWM3	
DRAWN BY JsP		DRAWING NO. 01247-41 SHEET 1 OF 2	
DATE 10-2-03			
CHK'D			
MATERIAL: 16 GAGE C.R.S.			
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .03(.8) ANGLES ±			

REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH
R	10-2-03	JsP		RELEASED TO PRODUCTION	01247-41					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

PZAEWM3