




PANDUIT PART NO.	NOMINAL DIAMETER	DIMENSIONS					WEIGHT	
		'A'	'B'	'C'	'D'	'E'	grams	100 pcs
CTH87U22-...30	22	25.4	22.7	14.3	34.2	12.0	405	
CTH62U17-...30	17	21.2	17.9		34.0		376	
CTH50U13-...30	13	15.8	13.7		27.0	10.0	248	
CTH38U10-...30	10	13.0	11.0		23.2		220	
CTH35U08-...30	8.5	11.7	9.4		21.7		197	
CTH19U04-...30	4.5	7.1	5.1		14.2		153	



NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION CONCERNING PACKAGE SIZE, PART MATERIAL AND PART COLOR.
- MATERIAL:
HEAT STABILIZED NYLON 6/6
COLOR:
BLACK
- DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
- PANEL THICKNESS:
2.0 - 3.2
HOLE DIAMETER:
8.8 - 11.0

CAD FILENAME/LAYERS		G01932BP_PB_CTHMNTS_06	
PANDUIT CORP.		TINLEY PARK, ILLINOIS	
CTH__U__		CORRUGATED TUBING HOLDER WITH PUSH MOUNT AND UMBRELLA	
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE METRIC TOLERANCE: ±0.5			
DRAWN BY	MLD	MAT'L:	SCALE NONE
DATE	10-6-98	SEE NOTE 2	DRAWING NO.
CHK'D	KUN		GB1932BP
			DWG SIZE A

6	6-11-07	TMSA	RR	ADDED "E" DIMENSIONS	GB1932BP	6	KUN		
5	10-24-05	TMSA		REMOVED HEIGHT REF DIMENSION	GB1932BP	5			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CTH87U22-C30](#) [CTH19U04-C30](#)