

J Hook Cable Support System Cross Reference



J-PRO™ Cable Support System

- J Hooks available in 3/4", 1 5/16", 2", and 4" bundle capacities to meet requirements of a variety of applications throughout the physical infrastructure
- Complete horizontal and vertical 1" bend radius control helps prevent degradation of cable performance
- UL and CAN/ULC listed and suitable for use in air handling spaces
- Color options provide means to segregate and identify cable bundles for specific applications, such as data, voice, security, fire alarm or other applications that require a designated pathway
- Pre-riveted assemblies allow for attachment to ceilings, beams, threaded rods, drop wires and under floor supports to meet requirements of a variety of applications
- Cable tie channel allows user to install 3/4" *TAK-TY*® Cable Tie and provides a method to retain and manage cable bundles
- Non-metallic J Hook prevents cables from coming in contact with metal



Part Description	ERICO (CADDY*)	B-Line	PANDUIT
Wall Mount	CAT12	BCH12	JP75W-L20^ or JP75WP-L20^
	CAT21	BCH21	JP131W-L20 or JP131WP-L20
	CAT32	BCH32	JP2W-L20^‡** or JP2WP-L20^
	CAT64	BCH64	JP4W-X20^‡** or JP4WP-X20
Ceiling Mount	CAT12AB	BCH12-RB	JP75CM-L20^
	CAT21AB	BCH21-RB	JP131CM-L20
	CAT21AFAB3		JP131CM-L20
	CAT21AFAB4		JP131CM-L20
	CAT21AFAB6		JP131CM-L20
	CAT32AB	BCH32-RB	JP2CM-L20^
	CAT32AFAB3		JP2CM-L20^
	CAT32AFAB4		JP2CM-L20^
	CAT32AFAB6		JP2CM-L20^
	CAT64AB	BCH64-RB	JP4CM-X20
	CAT64AFAB3		JP4CM-X20
	CAT64AFAB4		JP4CM-X20
Drop Wire and Threaded Rod Clip	CAT124Z34	BCH12-W2	JP75DW-L20^
	CAT126Z34	BCH12-W6	JP75DW-L20^
	CAT214Z34	BCH21-W2	JP131DW-L20
	CAT216Z34	BCH21-W6	JP131DW-L20
	CAT324Z34	BCH32-W2	JP2DW-L20^‡
	CAT326Z34	BCH32-W6	JP2DW-L20^‡
Purlin Clips	CAT12AF14	BCH12-F4	JP75ZP-L20
	CAT12VF14	BCH12-F3	JP75CP-L20
	CAT21AF14	BCH21-F4	JP131ZP-L20
	CAT21VF14	BCH21-F3	JP131CP-L20
	CAT32AF14	BCH32-F4	JP2ZP-L20
	CAT32VF14	BCH32-F3	JP2CP-L20
	CAT64AF14	BCH64-F4	JP4ZP-X20
	CAT64VF14	BCH64-F3	JP4CP-X20

*CADDY is a registered trademark of ERICO International Corporation.

^Available in red. Replace -L20 with -L2 or -X20 with -X2 in part number suffix.

‡Available in blue. Replace -L20 with -L6 or -X20 with -X6 in part number suffix.

**Available in natural (white). Replace -L20 with -L or -X20 with -X in part number suffix.

J-Pro™ Cable Support System



JP2SBC50-L20



JP2SBC87-L20



JP2SBC50R-L20



JP2SBC87R-L20



JP2HBC25R-L20

JP2HBC50R-L20

JP2HBC75R-L20



JP2UF100-L20

Part Description	ERICO (CADDY*)	B-Line	PANDUIT
Screw-On Beam Clamp	CAT12BC		JP75SBC50-L20
	CAT12BC200		JP75SBC87-L20
	CAT12BCB	BCH12-C2	JP75SBC50R-L20^
	CAT12BC200B	BCH12-C442	JP75SBC87R-L20
	CAT21BC		JP131SBC50-L20
	CAT21BC200		JP131SBC87-L20
	CAT21BCB	BCH21-C2	JP131SBC50R-L20
	CAT21BC200B	BCH21-C442	JP131SBC87R-L20
	CAT32BC		JP2SBC50-L20
	CAT32BC200		JP2SBC87-L20
	CAT32BCB	BCH32-C2	JP2SBC50R-L20^**
	CAT32BC200B	BCH32-C442	JP2SBC87R-L20
	CAT64BC		JP4SBC50-X20
	CAT64BC200		JP4SBC87-X20
	CAT64BCB	BCH64-C2	JP4SBC50R-X20
	CAT64BC200B	BCH64-C442	JP4SBC87R-X20
Hammer-On Beam Clamp	CAT1224SM	BCH12-E-2-4	JP75HBC25R-L20
	CAT1258SM	BCH12-E-5-8	JP75HBC50R-L20
	CAT1291SM	BCH12-E-9-12	JP75HBC75R-L20
	CAT1224	BCH12-U-2-4	JP75HBC25R-L20
	CAT1258	BCH12-U-5-8	JP75HBC50R-L20
	CAT12912	BCH12-U-9-12	JP75HBC75R-L20
	CAT2124SM	BCH21-E-2-4	JP131HBC25R-L20
	CAT2158SM	BCH21-E-5-8	JP131HBC50R-L20
	CAT21912SM	BCH21-E-9-12	JP131HBC75R-L20
	CAT2124	BCH21-U-2-4	JP131HBC25R-L20
	CAT2158	BCH21-U-5-8	JP131HBC50R-L20
	CAT21912	BCH21-U-9-12	JP131HBC75R-L20
	CAT3224SM	BCH32-E-2-4	JP2HBC25R-L20
	CAT3258SM	BCH32-E-5-8	JP2HBC50R-L20
	CAT32912SM	BCH32-E-9-12	JP2HBC75R-L20
	CAT3224	BCH32-U-2-4	JP2HBC25R-L20
	CAT3258	BCH32-U-5-8	JP2HBC50R-L20
	CAT32912	BCH32-U-9-12	JP2HBC75R-L20
	CAT6424SM		JP4HBC25R-X20
	CAT6458SM		JP4HBC50R-X20
	CAT64912SM		JP4HBC75R-X20
	CAT6424	BCH64-U-2-4	JP4HBC25R-X20
	CAT6458	BCH64-U-5-8	JP4HBC50R-X20
	CAT64912	BCH64-U-9-12	JP4HBC75R-X20
Under Floor Pedestal Support Clamp	CAT12CD1B	BCH12-L1410	JP75UF100-L20
	CAT21CD1B	BCH21-L1410	JP131UF100-L20
	CAT32CD1B	BCH32-L1410	JP2UF100-L20
	CAT64CD1B	BCH64-L1410	JP4UF100-X20

*CADDY is a registered trademark of ERICO International Corporation.

^Available in red. Replace -L20 with -L2 in part number suffix.

**Available in natural (white). Replace -L20 with -L or -X20 with -X in part number suffix.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.3767.7011

PANDUIT LATIN AMERICA
Jalisco, Mexico
cs-la@panduit.com
Phone: 52.333.777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of PANDUIT product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800-777-3300 and reference WACR08



©2008 PANDUIT Corp.
ALL RIGHTS RESERVED.
Printed in the U.S.A.

SA-WACR08
8/2008

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[JP75HBC50R-L20](#) [JP4CM-X20](#) [JP4HBC25R-X20](#) [JP4HBC50R-X20](#)