


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	MAX. BUNDLE DIA. in [mm]	RECM. FASTENER	WEIGHT lb/g/100 pcs
RER2.0-S6	2.0 (50.8)	# 6 SCRW. (M3)	7.7 (3523)

NOTES:
1. SEE CURRENT PRICE SHEET FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE.

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS W10035DR/00 SH4 Ref: G03637BH/04

PANDUIT CORP TINLEY PARK, ILLINOIS

ELASTIC RETAINER, RER2.0-S6

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1 [2.5] (.XXX) ± .1
(.XX) ± .02 [1.5] ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION

DRAWN BY
GILES

MAT'L:

SCALE

DATE
3/16/10

CHK'D

DRAWING NO.

SS-41990

DWG

SIZE

R	3/16/10	BWG	MPH	INITIAL DRAWING RELEASE.	SS-41990	R		BOBK		DATE	3/16/10	DWG	B
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	CHK'D		SS-41990	SIZE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[RER2.0-S6-X](#)