


PANDUIT P/N	LENGTH	WEIGHT
T45C••8	96.00 ±.18 (2438 ±4.6)	1.35 LB/96 IN (612.4 G/2438 mm)
T45C••10	120.00 ±.18 (3048 ±4.6)	1.69 LB/120 IN (766.6 G/3048 mm)
T45C••2	78.74 ±.18 (2000 ±4.6)	1.11 LB/78.7 IN (503.5 G/2000 mm)
T45C••3	118.11 ±.18 (3000 ±4.6)	1.66 LB/118.1 IN (753.0 G/3000 mm)



1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. THE T45C IS USED WITH THE T45B.
3. DIMENSIONS IN PARENTHESIS ARE IN METRIC.

										CAD FILENAME/LAYERS										D38186BA_DC_T45C_00B.PRT									
										PANDUIT										CORP. TINLEY PARK, ILLINOIS									
										T-45 COVER (T45C)																			
																				REVISED PROFILE									
																				CUSTOMER DRAWING									
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (,X) ± (,XXX) ±.015(,38) (,XX) ±.031(,8) ANGLES ±										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.									
I	06/04/02	JBN	BKR	A. REVISED TITLE						38186-02	RGRO	RGRO							DRAWN BY		MAT'L:		SCALE		NONE				
R	10/16/01	JBN	BKR	RELEASED TO PRODUCTION						38186-02	RGRO	RGRO							JBN		PVC		DRAWING NO.		DWG				
																				DATE			10/16/01		38186-02		A		
REV	DATE	BY	CHK	DESCRIPTION						ECN	CHK	CUST	SUP							CHECKED BY			BKR		SIZE				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[T45CIW8](#) [T45CIW10](#) [T45CEI8](#) [T45CEI10](#)