


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	LENGTH	WEIGHT
T45DW8	96.00 $\pm$.18 (2438 $\pm$ 4.6)	.36 LB/96 IN (163.7 G/2438 mm)
T45DW10	120.00 $\pm$.18 (3048 $\pm$ 4.6)	.45 LB/120 IN (204.6 G/3048 mm)
T45DW2 (SEE NOTE 4)	78.7 $\pm$.18 (2000 $\pm$ 4.6)	.30 LB/78.7 IN (134.2 G/2000 mm)
T45DW3 (SEE NOTE 4)	118.1 $\pm$.18 (3000 $\pm$ 4.6)	.20 LB/118.1 IN (201.4 G/3000 mm)



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. THE T45DW SNAPS ONTO RAILS IN THE T45 RACEWAY BASE TO CREATE SEPARATE CHANNELS.
3. DIMENSIONS IN PARENTHESIS ARE IN METRIC.
4. METRIC LENGTHS ONLY AVAILABLE OUTSIDE NORTH AMERICA.

CAD FILENAME/LAYERS

D36975DV_DC_T45DW_00B.PRT

PANDUIT

CORP. TINLEY PARK, ILLINOIS

T-45 RACEWAY DIVIDER WALL
(T45DW8, T45DW10, T45DW2, T45DW3)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) $\pm$ (.XXX) $\pm$
(.XX) $\pm$.03(.8) ANGLES $\pm$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

1	06-16-00	JHNU	HIW	A. REVISED NOTE 4: ADDED METRIC LENGTHS	36975-57	HIW	HIW			DRAWN BY RABO	MAT'L: PVC	SCALE NONE	
R	10-28-99	RABO	HIW	RELEASED TO PRODUCTION.	36975-57	HIW	HIW			DATE 10-28-99		DRAWING NO. 36975-57	DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP		CHECKED BY BKR			SIZE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[T45DW10](#) [T45DW2](#) [T45DW8](#)