


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	LENGTH	WEIGHT
T70C**6	72.00 ±.13 (1829 ±3.0)	.9 LB/72 IN (409 G/1829 mm)
T70C**8	96.00 ±.13 (2438 ±3.0)	1.2 LB/96 IN (545 G/2438 mm)
T70C**10	120.00 ±.13 (3048 ±3.0)	1.5 LB/120 IN (682 G/3048 mm)
T70C**2 (SEE NOTE 5)	(2000 mm ±3.0)	.98 LB/78.7 IN (447 G/2000 mm)

- NOTES:
- SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 - THE T70C IS USED WITH THE T70B, T702B, AND TG70B.
 - DIMENSIONS IN PARENTHESIS ARE IN METRIC.
 - USE TWO (2) FEET OF T70C (COVER) FOR EVERY ONE (1) FOOT OF T702B (BASE).
 - ONLY AVAILABLE OUTSIDE NORTH AMERICA.



CAD FILENAME/LAYERS D35541CA_DC-T70C-03A.PRT

PANDUIT				CORP. TINLEY PARK, ILLINOIS			
T70 RACEWAY COVER				(T70C**6, T70C**8, T70C**10, T70C**2) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .010(.3) (.XX) ± .03(.8) ANGLES ±				UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
DRAWN BY JBA				SCALE NONE			
DATE 09-19-96				MATERIAL: PVC			
CHECKED BY CEF				DRAWING NO. 35541-27			
REV				SIZE A			

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
4	05-18-04	JBN	BKR	G. REMOVED T70C**3 PART NUMBER F. RENAMED CAD FILE	35541-27	RGRD	RGRD	
3	04-14-00	MSO	CAZ	E. REVISED NOTE 2 TO INCLUDE TG70B	35541-27	H1W	H1W	
2	10-20-98	DW	H1W	D. ADDED NOTE 5 C. ADDED 3M LENGTH AND WEIGHT	35541-27	H1W	H1W	
1	07-08-98	DW	H1W	A. ADDED COVER SIZES. B. ADDED NOTE 4	35541-27	H1W	H1W	
R	09-19-96	JBA	CEF	RELEASED TO PRODUCTION	35541-27	CEF		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[T70CIW8](#) [T70CEI10](#) [T70CIW6](#) [T70CWH10](#) [T70CIW10](#) [T70CEI6](#) [T70CEI8](#) [T70CWH6](#) [T70CWH8](#)