



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




#12-24
BONDING STUD (QTY. 2)




#12-24
BONDING NUT (QTY. 6)




#12-24
SLOTTED HEX-HEAD ZINC PLATED
THREAD-FORMING SCREW (QTY. 1)



#10-32
SLOTTED HEX-HEAD ZINC PLATED
THREAD-FORMING SCREW (QTY. 2)



#12 LOCK WASHER (QTY. 3)



CLEANING PAD (QTY. 1)



5cc TUBE ANTI-OXIDANT PASTE (QTY. 1)

NOTES:


1. MINI-TR GROUNDING KIT
PART NUMBERS: PZCGK
2. PACKAGING: 1 KIT PER BAG
3. DIMENSIONS IN PARENTHESIS ARE MILLIMETERS.
4. ALL COMPONENTS THAT MAKE UP THIS KIT
ARE RoHS COMPLIANT.




LISTED
GROUNDING AND BONDING EQUIPMENT



CERTIFIED



FACTORY CRIMPED #10 FLEX MAIN JUMPER GREEN/YELLOW INSULATION (QTY. 1)



FACTORY CRIMPED #10 FLEX DOOR JUMPER GREEN/YELLOW INSULATION (QTY. 1)

C41683_01

PANDUIT

CORP. TINLEY PARK, ILLINOIS

MINI-TR GROUNDING KIT
(PZCGK)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ± ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION

REV	DATE	BY	CHK
01	11/06	JHNU	JHNU
00	10/06	JHNU	JMAR

DESCRIPTION	ECN	PM	CUST
REVISED LUG ON #10 FLEX MAIN JUMPER: 90 DEGREE LUG WAS 45 DEGREE LUG	PC00594		
DRAWING RELEASED	PC00574		

DATE	CHK'D
10/06	

DRAWN BY	MAT'L:
JHNU	

SCALE	DRAWING NO / CAD FILE
NONE	C41683

DWG B SIZE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

PZCGK