




NOTES:

1. TERMINATED WITH (8 POSITION) UTP MODULAR PLUGS ON BOTH ENDS PER T568B.
2. CONSTRUCTED WITH 4-PR/26AWG STRANDED F/UTP CAT6A PATCH CABLE
3. MATERIAL:
PLUG: POLYCARBONATE
BOOT: THERMOPLASTIC RESIN
4. FLAMMABILITY RATING: CM/LSZH DUAL RATED

T568B WIRING SCHEME	
PLUG POSITION:	CABLE WIRE:
1	WHITE/ORANGE
2	ORANGE
3	WHITE/GREEN
4	BLUE
5	WHITE/BLUE
6	GREEN
7	WHITE/BROWN
8	BROWN

CABLE COLORS	** = COLOR
OFF WHITE	--
BLACK	BL
BLUE	BU
RED	RD
YELLOW	YL
GREEN	GR
GRAY	GY

PANDUIT PART NUMBER	MIN. CABLE LENGTH
NK6APC3**	3 FT
NK6APC5**	5 FT
NK6APC7**	7 FT
NK6APC10**	10 FT
NK6APC14**	14 FT
NK6APC20**	20 FT
NK6APC1M**	1 METER
NK6APC2M**	2 METERS
NK6APC3M**	3 METERS
NK6APC4M**	4 METERS
NK6APC5M**	5 METERS
NK6APC7M**	7 METERS
NK6APC10M**	10 METERS
NK6APC15M**	15 METERS

PART NUMBER		NK6APCXX**	
TITLE			
NETKEY CATEGORY 6A UTP PATCH CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME		14M504BB/00	
DATASET FILE NAME		14M504BB_DC02/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ± .03 (.8)		SEE NOTE 3	
.XXX ± .010 (.3)		DRAWING NUMBER:	
ANGLES ±		14M504BB-02	
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
BJN	10-21-14	SCAL	NONE
SHT 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
R	10-21-14	BJN	SCAL	LPH	RELEASED TO PRODUCTION	14M504BB-02

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[NK6APC1](#) [NK6APC13RD](#) [NK6APC11BL](#) [NK6APC12BL](#) [NK6APC13GY](#) [NK6APC11](#) [NK6APC12RD](#) [NK6APC15BU](#)
[NK6APC16GY](#) [NK6APC17GY](#) [NK6APC2GR](#) [NK6APC11BU](#) [NK6APC11GR](#) [NK6APC11RD](#) [NK6APC12GY](#)
[NK6APC13YL](#) [NK6APC15GY](#) [NK6APC17BU](#) [NK6APC19RD](#) [NK6APC1GR](#) [NK6APC11GY](#) [NK6APC11YL](#)
[NK6APC12](#) [NK6APC13](#) [NK6APC13GR](#) [NK6APC17](#) [NK6APC2BL](#) [NK6APC12GR](#) [NK6APC16BU](#) [NK6APC16GR](#)
[NK6APC18GR](#) [NK6APC13BU](#) [NK6APC16BL](#) [NK6APC18](#) [NK6APC1BL](#) [NK6APC12BU](#) [NK6APC12YL](#)
[NK6APC18BU](#) [NK6APC18RD](#) [NK6APC19](#) [NK6APC19BU](#) [NK6APC2](#) [NK6APC2YL](#) [NK6APC15](#) [NK6APC15BL](#)
[NK6APC15GR](#) [NK6APC15YL](#) [NK6APC19GY](#) [NK6APC1GY](#) [NK6APC4](#) [NK6APC16](#) [NK6APC17GR](#) [NK6APC17RD](#)
[NK6APC13BL](#) [NK6APC16RD](#) [NK6APC19GR](#) [NK6APC19YL](#) [NK6APC15RD](#) [NK6APC16YL](#) [NK6APC17BL](#)
[NK6APC18BL](#) [NK6APC19BL](#) [NK6APC2BU](#) [NK6APC18GY](#) [NK6APC18YL](#) [NK6APC1BU](#) [NK6APC4BL](#) [NK6APC6BU](#)
[NK6APC9BL](#) [NK6APC4BU](#) [NK6APC6BL](#) [NK6APC6RD](#) [NK6APC8](#) [NK6APC6](#) [NK6APC6GY](#) [NK6APC6YL](#)
[NK6APC9RD](#) [NK6APC1RD](#) [NK6APC2RD](#) [NK6APC9GR](#) [NK6APC17YL](#) [NK6APC2GY](#) [NK6APC4GR](#) [NK6APC4YL](#)
[NK6APC8GR](#) [NK6APC8GY](#) [NK6APC9GY](#) [NK6APC4RD](#) [NK6APC4GY](#) [NK6APC8RD](#) [NK6APC8YL](#) [NK6APC8BU](#)
[NK6APC9YL](#) [NK6APC6GR](#) [NK6APC8BL](#) [NK6APC9BU](#) [NK6APC1YL](#) [NK6APC9](#)