
### **Unshielded Patch Cords**

- 100% testing of all cords to component standards
- Patented tangle-free latch on all plugs
- Offered in a wide variety of colors and lengths
- All cords support PoE, PoE+, and PoE++
- Category 6A now available in 28 AWG
- All 28 AWG cords are less than 50% the size of traditional 24 AWG cords

#### **Cord diameter comparison**



diameter to scale1

## 28 AWG



UTP28SP\*^

 Supports up to 96 meters of channel length (when using 6 meters of patch) · Dual CM/LSZH flame rating

· 28 AWG; De-rating factor: 1.9

Part Number (feet)	Part Number (meters)	Description	Standard Lengths
UTP28X*^	UTP28X*M^	Category 6A Performance 28 AWG UTP Patch Cord	1 – 50 ft. (every 1 ft.) 55 – 130 ft. (every 5 ft.)
UTP28SP*^	UTP28SP*M^	Category 6 Performance 28 AWG UTP Patch Cord	0.5 – 10m (every 0.5m)
UTP28CH*^	UTP28CH*M^	Category 5e Performance 28 AWG UTP Patch Cord	11 – 20m (every 1m) 25 – 40m (every 5m)

## TX6A-SD<sup>T</sup>



UTP6ASD\*^

· Supports full 100-meter Category 6A channel while using 24% less space than 24 AWG Category 6A cords

• CM flame rating and available LSZH option for meter lengths

• 26 AWG; De-rating factor: 1.5

Part Number (feet)	Part Number (meters)	Description	Standard Lengths
UTP6ASD*^	UTP6ASD*M^	Category 6A TX6A™ 10Gig™ 26 AWG UTP Patch Cord with MaTriX Technology	1 – 50 ft. (every 1 ft.) 55 – 195 ft. (every 5 ft.) 0.5 – 10m (every 0.5m)
* = Length ^ = Cord color (see below).			11 – 20m (every 1m) 25 – 60m (every 5m)

# TX6A™, TX6™ PLUS and TX5e™



UTP6A\*^

- · Supports full 100-meter channel
- 24 AWG; De-rating factor: 1.2
- · CM flame rating with LSZH option for Category 6 & 5e (meter lengths only)

Part Number (feet)	Part Number (meters)	Description	Standard Lengths
UTP6A*^	UTP6A*M^	Category 6A TX6A™ 10Gig™ 24 AWG UTP Patch Cord with MaTriX Technology	1 – 50 ft. (every 1 ft.) 55 – 200 ft. (every 5 ft.)
UTPSP*^Y	UTPSP*M^Y	Category 6 TX6 <sup>™</sup> PLUS 24 AWG UTP Patch Cord	0.5 – 10m (every 0.5m) 11 – 20m (every 1m) 25 – 60m (every 5m)
UTPCH*^Y	UTPCH*M^Y	Category 5e TX5e™ 24 AWG UTP Patch Cord	

<sup>\* =</sup> Lenath

^ = Cord color (see below).

Available cord colors





<sup>^ =</sup> Cord color (see below). Pink (PK) available as cord color option for UTP28SP only. Pastel Blue (PB) and Pastel Green (PG) available as cord color options for UTP28SP and UTP28CH in Asia Pacific Region only.

#### **Shielded Patch Cords**

- Dual-rated CM/LSZH flame rating
- · Patented tangle-free latch on all plugs
- All cords support PoE, PoE+, and PoE++
- Multiple Category 6A cord choices
- · Category 6A now available in 28 AWG

#### **Cord diameter comparison**



[Approximate cord diameter to scale]

### 28 AWG

• Supports up to 96 meters of channel length (when using 6 meters of patch)

• 28 AWG; De-rating factor: 1.9



STP28X\*M^

Part Number (feet)	Part Number (meters)	Description	Standard Lengths
Not available	STP28X*M^	Category 6A Performance 28 AWG F/UTP Shielded Patch Cord	0.5 – 10m (every 0.5m) 11 – 20m (every 1m) 25 – 40m (every 5m)

<sup>\* =</sup> Length

### TX6A™ and TX5e™

Supports full 100-meter channel

26 AWG; De-rating factor: 1.5



STP6X\*M^

Part Number (feet)	Part Number (meters)	Description	Standard Lengths
STP6X*^	STP6X*M^	Category 6A TX6A™ 10Gig™ 26 AWG S/FTP Shielded Patch Cord	1 – 50 ft. (every 1 ft.) 55 – 200 ft. (every 5 ft.) 0.5 – 10m (every 0.5m) 11 – 20m (every 1m) 25 – 60m (every 5m)
Not available	STP6C*M^	Category 6A TX6A™ 10Gig™ 26 AWG F/UTP Shielded Patch Cord	
Not available	STPCH*MB#	Category 5e TX5e <sup>™</sup> 26 AWG F/UTP Shielded Patch Cord	

<sup>\* =</sup> Length

<sup># =</sup> Boot color. Color options for boots are BL, BU, GR, RD, YL, BR (Brown).



IG=Int'l Gray, BL=Black, BU=Blue, GR=Green, RD=Red, OR=Orange, VL=Violet, YL=Yellow, Off White (no designation, default for STP6C), GY=Gray. Note: Colors shown may vary slightly from actual cable colors.

#### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575

PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

#### For more information

Contact Customer Service by email: cs@panduit.com or by phone: 800-777-3300

©2015 Panduit Corp. ALL RIGHTS RESERVED. COSG11--WW-ENG 12/2015



<sup>^ =</sup> Cord color (see below).

<sup>^ =</sup> Cord color (see below).

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

#### Panduit:

UTPSP24BUY UTPSP24VLY UTPSP50BUY UTP28X3GR UTP28X5 UTP28X5RD UTP28X30MVL UTP28X5YL
UTP28X6 UTP28X7BU UTP28X15BU UTP28X5BL UTP28X7GR UTP28X3BU UTP28X5OR UTP28X7
UTP28X10BU UTP28X10GR UTP28X1BU UTP28X45 UTP28X5GR UTP28X9 UTP28X4 UTP28X7RD
UTP28X1YL UTP28X3RD UTP28X5BU UTP28X7YL UTP28X10BL UTP28X10YL UTP28X3BL UTP28X3
UTP28X2YL UTP28X3YL UTP28X3VL UTP28X4BU UTP28X4BU UTP28X85GY UTP6A2 UTP6A1BU UTP6ASD85GY
UTP6ASD1 UTP6A60 UTP6ASD105 UTP6ASD7 UTP6ASD10 UTP6ASD10BU UTP6ASD15MBU UTPSP14GYY
UTP6ASD5 UTPSP10GYY UTP6ASD5BU UTP6ASD7YL UTPSP15GYY UTPSP5GYY UTPSP6GYY UTPSP7GYY
UTP28SP120 UTP28X3MOR UTPSP23GYY UTPSP27GYY UTPCH45MGRY UTPCH55MBUY
UTPCH3.5MRDY UTPCH3.5MGYY UTPCH45MVLY UTPCH60MORY UTPCH55MVLY UTPCH55MBUY
UTPCH60MYLY UTPCH4.5MGYY UTPCH4.5MORY UTPCH55MBLY UTPSP30MGYY UTPCH3.5MRDY
UTPCH45MRDY UTPCH4.5MGRY UTPCH4.5MBLY UTPCH60MVLY UTPCH55MGRY UTPCH55MRDY
UTPCH45MBUY UTPCH4.5MGRY UTPCH4.5MBLY UTPCH60MVLY UTPCH55MGRY UTPCH50MYLY
UTPCH45MBUY UTPCH3.5MGRY UTPCH4.5MRDY UTPCH4.5MRDY UTPCH60MBLY UTPCH50MBLY
UTPCH3.5MVLY UTPCH3.5MYLY UTPCH4.5MRDY UTPCH4.5MVLY UTPCH60MBLY UTPCH50MBLY
UTPCH3.5MVLY UTPCH3.5MYLY UTPCH50MVLY UTPCH3.5MORY UTPCH60MGRY UTPCH4.5MYLY
UTPCH50MBUY