


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	MIN. CABLE LENGTH	WEIGHT
ISTP6X1MBL	1 M	1.82 lbs/10 PCS (825.8 g/10 PCS)
ISTP6X2MBL	2 M	3.64 lbs/10 PCS (1651.6 g/10 PCS)
ISTP6X3MBL	3 M	5.46 lbs/10 PCS (2477.5 g/10 PCS)
ISTP6X5MBL	5 M	9.10 lbs/10 PCS (4129.1 g/10 PCS)
ISTP6X10MBL	10 M	18.20 lbs/10 PCS (8,258 ka/10 PCS)

NOTES :

- NOTES
- **1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. CABLE MEETS CATEGORY 6A REQUIREMENTS AND CURRENT ODVA REQUIREMENTS FOR INDUSTRIAL CABLE.
5. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.


T568B WIRING

PLUG POSITION

1
2
3
4
5
6
7
8

CABLE WIRE
WHITE ORANGE
ORANGE
WHITE GREEN
BLUE
WHITE BLUE
GREEN
WHITE BROWN
BROWN

- PLUG CAPS

PART NUMBER		ISTP6X*MBL	
TITLE			
CATEGORY 6A INDUSTRIALNET, SFTP, PATCH CORDS WITH PANDUIT PLUG CAPS			
CUSTOMER DRAWING			
ITEM REVISION NAME		00251NAC/01	
DATASET FILE NAME		00251NAC_DC02/01A	
<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]</p> <p>.X ± .XXX ± .010 [.3]</p> <p>.XX ± .03 [.8]</p> <p>ANGLES ±</p>  <p>THIRD ANGLE PROJECTION</p>		<p>PANDUIT</p> <p>MATERIAL :</p> <p>DRAWING NUMBER:</p> <p>00251NAC-02</p>	
DRAWN BY	DATE	CHK	SCALE
BJN	7-22-16	SCAL	NONE
SHT 1 OF 1			SIZE
			A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[ISTP6X3MBL](#) [ISTP6X10MBL](#) [ISTP6X2MBL](#) [ISTP6X5MBL](#) [ISTP6X1MBL](#)