

Search within category

GO

BUY NOW

DESIGN / INSTALL



FXURLEN74YNM025

OM3 24-fiber, Interconnect, LSZH, 24F MPO Female to (2) 12-fiber Female PanMPO, Method B, Optimized IL, 25 Meters, Aqua.

- Specs
- Packaging Details
- Documents
- ★ Add to Favorites
- 🛒 Add to BOM

Application	Data centers requiring quick infrastructure deployment with extended reach that want to maintain bandwidth throughout the infrastructure.
Assembly Length Range	20-29 m (66-98 ft)
Cable Color	Aqua
Connector 1 Type	24F MPO
Connector 2 Type	(2)12F MPO
Fiber Type	OM3
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Length (ft.)	82
Length (m)	25
Standards	TIA/EIA-598-C.3, Plenum Rated NFPA-262, LSZH-Rated, Meet IEC-60332, RoHS Compliant
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FXURLN74YNM025](#)