

infrastructure for a connected world

UNITED STATES | [CHANGE] | ENGLISH | REGISTER / LOG IN | FOLLOW US

PANDUIT

SOLUTIONS | PRODUCTS AND SERVICES | SUPPORT | ABOUT US

Search Panduit.com

GO

Search within category

GO

BUY NOW

DESIGN / INSTALL

FXURLENENXNM019

OM3 24-fiber, Interconnect, LSZH, 24F MPO Female to 24F MPO Female, Method A, Optimized IL, 19 m, Aqua.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Application	Data centers requiring quick infrastructure deployment with extended reach that want to maintain bandwidth throughout the infrastructure.
Assembly Length Range	10-19 m (33-65 ft)
Cable Color	Aqua
Connector 1 Type	24F MPO
Connector 2 Type	24F MPO
Fiber Count	24
Fiber Type	OM3
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Length (ft.)	62.32
Length (m)	19.00
Standards	TIA/EIA-598-C.3, Plenum Rated NFPA-262, LSZH-Rated, Meet IEC-60332, RoHS Compliant
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000

LEGAL INFORMATION | PRIVACY POLICY | CONTACT US | SITE MAP | WHERE TO BUY | JOBS | UNSUBSCRIBE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FXURLENENXNM019](#)