



SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com

GO

Search within category

GO

BUY NOW

DESIGN / INSTALL



FXURLEN74XNM020

OM3 24-fiber, Interconnect, LSZH, 24F MPO Female to (2) 12-fiber Female PanMPO, Method A, Optimized IL, 20 Meters, Aqua.

Specs

Packaging Details

Documents

Add to Favorites

Add to BOM

Application	Data centers requiring quick infrastructure deployment with extended reach that want to maintain bandwidth throughout the infrastructure.
Assembly Length Range	20-29 m (66-98 ft)
Cable Color	Aqua
Connector 1 Type	24F MPO
Connector 2 Type	(2)12F MPO
Fiber Type	OM3
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Length (ft.)	65.6
Length (m)	20
Standards	TIA/EIA-598-C.3, Plenum Rated NFPA-262, LSZH-Rated, Meet IEC-60332, RoHS Compliant
RoHS Compliance Status	Compliant
Min. Order Qty.	1.0000

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FXURLEN74XNM020](#)