



Search within category

GO

BUY NOW

DESIGN / INSTALL



FXUYLF5F5YAM051

24-Fiber OM3 HD Flex Indoor Small Diameter Trunk, LSZH, 24F MPO Male to 24F MPO Male, Method B, Optimized IL, Pulling Eye, 51 Meters, Aqua.

Specs

Packaging Details

Documents

★

Add to Favorites

🛒

Add to BOM

Application	10G fiber backbone or permanent link
Cable Color	Aqua
Connector 1 Type	24F MPO Male
Connector 2 Type	24F MPO Male
Fiber Count	24
Fiber Type	OM3
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Length (ft.)	167.28
Length (m)	51
Part Features	Minimize waste, optimize cable management, speed deployment, improve flexibility and manageability for lower installation costs.
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FXUYLF5F5YAM051](#)