

infrastructure for a connected world

UNITED STATES

[CHANGE]

ENGLISH

REGISTER / LOG IN

FOLLOW US

PANDUIT

SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com

GO

Search within category

GO

BUY NOW

DESIGN / INSTALL

FXURPEN74YNF022

OM3 24-fiber, Interconnect, Plenum, 24F MPO Female to (2) 12-fiber Female PanMPO, Method B, Optimized IL, 22 Feet, Aqua.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Application	Data centers requiring quick infrastructure deployment with extended reach that want to maintain bandwidth throughout the infrastructure.
Assembly Length Range	0-9 m (0-32 ft)
Cable Color	Aqua
Connector 1 Type	24F MPO
Connector 2 Type	(2)12F MPO
Fiber Cable Type	Multi mode 50/125
Fiber Count	24
Fiber Type	OM3
Flammability Rating	Plenum (OFNP)
Length (ft.)	22
Length (m)	6.71
Standards	TIA/EIA-598-C.3, Plenum Rated NFPA-262, LSZH-Rated, Meet IEC-60332, RoHS Compliant
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000

LEGAL INFORMATION

PRIVACY POLICY

CONTACT US

SITE MAP

WHERE TO BUY

JOBS

UNSUBSCRIBE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FXURPEN74YNF022](#)