

infrastructure for a connected world

UNITED STATES

[CHANGE]

ENGLISH

REGISTER / LOG IN

FOLLOW US

PANDUIT

SOLUTIONS

PRODUCTS AND SERVICES

SUPPORT

ABOUT US

Search Panduit.com

GO

Search within category

GO

BUY NOW

DESIGN / INSTALL

FZURLEN74XNM029

OM4 24-fiber, Interconnect, LSZH, 24F MPO Female to (2) 12-fiber Female PanMPO, Method A, Optimized IL, 29 Meters, Aqua.

Specs

Packaging Details

Documents

★ Add to Favorites

🛒 Add to BOM

Application	Data centers requiring quick infrastructure deployment with extended reach that want to maintain bandwidth throughout the infrastructure.
Assembly Length Range	20-29 m (66-98 ft)
Cable Color	Aqua
Connector 1 Type	24F MPO
Connector 2 Type	(2)12F MPO
Fiber Cable Type	Multi mode 50/125
Fiber Count	24
Fiber Type	OM4
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Length (ft.)	95.12
Length (m)	29
Standards	TIA/EIA-598-C.3, Plenum Rated NFPA-262, LSZH-Rated, Meet IEC-60332, RoHS Compliant
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000

LEGAL INFORMATION |

PRIVACY POLICY |

CONTACT US |

SITE MAP |

WHERE TO BUY |

JOBS |

UNSUBSCRIBE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FZURLN74XNM029](#)